




PRODUCT NUMBER

89006-XYLF





spec ref	*	dr	Terran Huang	2010/07/08	projection	mm	size	A4	scale	2:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Narayanan, Aru	2018/05/18			ecn no	ELX-I-30208-1		
ISO 406		chr	-	-			rel level	Released		
ISO 1101		appr	K-Paul Biju	2018/05/20	product family	METRAL				
surface	3.200 linear				title	METRAL SIGNAL HEADER	dwg no	89006	rev	BK
ISO 1302	angular				I MOD, 5 ROW PRESS-FIT					
	0.X				cat. no.	-	Product - Customer Drw	sheet 1 of 9		
	0.XX									
	0.XXX									
	0°									
	±0.3									
	±0.13									
	±0.050									
	±2°									



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
11	6.50	17.00
12	7.25	17.00
13	8.25	4.30
14	8.25	13.60
15	8.25	17.00
16	7.00	4.30
17	7.00	13.60
18	7.00	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
59	5.00	11.80

spec ref		*		dr	Terran Huang	2010/07/08	projection 		size	A4	scale	2:1	
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Narayanan, Aru	2018/05/18			ecn no	ELX-I-30208-1			
				chr	-	-			rel level				Released
				appr	K-Paul Biju	2018/05/20			product family		METRAL		
surface 3.200 linear  ISO 1302		0.X	±0.3	Amphenol FCI	title	METRAL SIGNAL HEADER I MOD, 5 ROW PRESS-FIT			dwg no	89006		rev	BK
		0.XX	±0.13										
		0.XXX	±.050										
		angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw			sheet 2 of 9		

A

B

C

D

METRAL P/N		ROW	CONTACT CODE MOD. I					
			1	2	3	4	5	6
89006-X10LF		E	I	I	I	I	I	
		D	I	I	I	I	I	
		C	I	I	I	I	I	
		B	I	I	I	I	I	
		A	I	I	I	I	I	

METRAL P/N		ROW	CONTACT CODE MOD. I					
			1	2	3	4	5	6
89006-X14LF		E	4	4	4	4	4	
		D	3	3	3	3	3	
		C	4	4	4	4	4	
		B	4	4	4	4	4	
		A	4	4	4	4	4	

METRAL P/N		ROW	CONTACT CODE MOD. I					
			1	2	3	4	5	6
89006-X19LF		E	4	4	4	4	4	
		D	4	4	4	4	4	
		C	4	4	4	4	4	
		B	4	4	4	4	4	
		A	4	4	4	4	4	

METRAL P/N		ROW	CONTACT CODE MOD. I					
			1	2	3	4	5	6
89006-X23LF		E	8	8	8	8	8	
		D	20	20	20	20	20	
		C	8	8	8	8	8	
		B	8	8	8	8	8	
		A	8	8	8	8	8	

METRAL P/N		ROW	CONTACT CODE MOD. I					
			1	2	3	4	5	6
89006-X27LF		E	6	6	6	6	6	
		D	6	6	6	6	6	
		C	6	6	6	6	6	
		B	6	6	6	6	6	
		A	20	20	20	20	20	

METRAL P/N		ROW	CONTACT CODE MOD. I					
			1	2	3	4	5	6
89006-X32LF		E	12	12	12	12	12	
		D	11	11	11	11	11	
		C	11	11	11	11	11	
		B	9	9	9	9	9	
		A	9	9	9	9	9	

 | </ |

spec ref		*		dr	Terran Huang	2010/07/08	projection 		mm	size	A4	scale	1:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Narayanan, Aru	2018/05/18			ecn no	ELX-I-30208-1						
ISO 406 ISO 1101				chr	-	-			rel level				Released			
				appr	K-Paul Biju	2018/05/20	product family			METRAL						
surface	3.200		linear	0.X	±0.3		Amphenol FCI	title	METRAL SIGNAL HEADER			dwg no	89006		rev	BK
				0.XX	±0.13											
				0.XXX	±.050											
ISO 1302		angular	0°	±2°		www.fci.com	cat. no.	-	Product - Customer Drw			sheet 3 of 9				

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X36LF	E	10	10	10	10	10	10
	D	10	10	10	10	10	10
	C	10	10	10	10	10	10
	B	10	10	10	10	10	10
	A	10	10	10	10	10	10

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X41LF	E	2	2	2	2	2	2
	D	1	1	1	1	1	1
	C	2	2	2	2	2	2
	B	2	2	2	2	2	2
	A	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X45LF	E	1	1	1	1	1	1
	D	19	19	19	19	19	19
	C	1	1	1	1	1	1
	B	19	19	19	19	19	19
	A	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X49LF	E	4	4	4	4	4	4
	D	3	3	3	3	3	3
	C	3	3	3	3	3	3
	B	3	3	3	3	3	3
	A	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X53LF	E	6	6	6	6	6	6
	D	6	6	6	6	6	6
	C	6	6	6	6	6	6
	B	6	6	6	6	6	6
	A	8	8	8	8	8	8

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X57LF	E	6	6	6	6	6	6
	D	7	7	7	7	7	7
	C	6	6	6	6	6	6
	B	6	6	6	6	6	6
	A	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X37LF	E	10	10	10	10	10	10
	D	10	10	10	10	10	10
	C	10	10	10	10	10	10
	B	10	10	10	10	10	10
	A	21	21	21	21	21	21

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X42LF	E	2	2	2	2	2	2
	D	4	4	4	4	4	4
	C	4	4	4	4	4	4
	B	3	3	3	3	3	3
	A	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X46LF	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
	C	4	4	4	4	4	4
	B	2	2	2	2	2	2
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X50LF	E	6	6	6	6	6	6
	D	6	6	6	6	6	6
	C	6	6	6	6	6	6
	B	8	8	8	8	8	8
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X54LF	E	5	5	5	5	5	5
	D	7	7	7	7	7	7
	C	8	8	8	8	8	8
	B	7	7	7	7	7	7
	A	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X58LF	E	20	20	20	20	20	20
	D	20	20	20	20	20	20
	C	20	20	20	20	20	20
	B	20	20	20	20	20	20
	A	20	20	20	20	20	20

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X39LF	E	12	12	12	12	12	12
	D	12	12	12	12	12	12
	C	12	12	12	12	12	12
	B	12	12	12	12	12	12
	A	12	12	12	12	12	12

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X43LF	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
	C	2	2	2	2	2	2
	B	2	2	2	2	2	2
	A	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X47LF	E	2	2	2	2	2	2
	D	3	3	3	3	3	3
	C	2	2	2	2	2	2
	B	2	2	2	2	2	2
	A	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X51LF	E	6	6	6	6	6	6
	D	5	5	5	5	5	5
	C	6	6	6	6	6	6
	B	6	6	6	6	6	6
	A	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X55LF	E	5	5	5	5	5	5
	D	20	20	20	20	20	20
	C	5	5	5	5	5	5
	B	20	20	20	20	20	20
	A	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X59LF	E	8	8	8	8	8	8
	D	7	7	7	7	7	7
	C	7	7	7	7	7	7
	B	7	7	7	7	7	7
	A	20	20	20	20	20	20

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X40LF	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
	C	2	2	2	2	2	2
	B	4	4	4	4	4	4
	A	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X44LF	E	1	1	1	1	1	1
	D	3	3	3	3	3	3
	C	4	4	4	4	4	4
	B	3	3	3	3	3	3
	A	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X48LF	E	19	19	19	19	19	19
	D	19	19	19	19	19	19
	C	19	19	19	19	19	19
	B	19	19	19	19	19	19
	A	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X52LF	E	6	6	6	6	6	6
	D	8	8	8	8	8	8
	C	8	8	8	8	8	8
	B	7	7	7	7	7	7
	A	8	8	8	8	8	8

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X56LF	E	6	6	6	6	6	6
	D	6	6	6	6	6	6
	C	8	8	8	8	8	8
	B	6	6	6	6	6	6
	A	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
89006-X60LF	E	10	10	10	10	10	10
	D	10	10	10	10	10	10
	C	10	10	10	10	10	10
	B	12	12	12	12	12	12
	A	10	10	10	10	10	10

spec ref		*		dr		Terran Huang	2010/07/08		projection				size		A4		scale		1:1		
tolerance std		ISO 406		eng		Narayanan, Aru		2018/05/18						ecn no		ELX-I-30208-1		rel level		Released	
ISO 1101		TOLERANCES UNLESS OTHERWISE SPECIFIED		chr		-		-		product family		METRAL		rel level		Released					
surface		3.200 linear		appr		K-Paul Biju		2018/05/20		product family		METRAL		rel level		Released					
ISO 1302		angular		0°		±2°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 4 of 9					

spec ref	*	dr	Terran Huang	2010/07/08	projection	mm	size	A4	scale	1:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Narayanan, Aru	2018/05/18			ecn no	ELX-I-30208-1		
ISO 406		chr	-	-			rel level	Released		
ISO 1101		appr	K-Paul Biju	2018/05/20	product family	METRAL				
surface	3.200 linear	0.X	±0.3	Amphenol FCI	title	METRAL SIGNAL HEADER	dwg no	89006	rev	BK
		0.XX	±0.13	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 6 of 9		
		0.XXX	±0.050							
ISO 1302	angular	0°	±2°							

METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X109LF	E	59	59	59	59	59	59
	D	59	59	59	59	59	59
	C	59	59	59	59	59	59
	B	59	59	59	59	59	59
	A	7	7	7	7	7	7
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X113LF	E	6	6	6	6	6	5
	D	6	6	6	6	6	6
	C	6	6	6	6	6	6
	B	6	6	6	6	6	6
	A	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X117LF	E	6	6	6	6	6	6
	D	8	6	6	6	6	6
	C	6	6	6	6	6	6
	B	6	8	6	6	6	6
	A	6	8	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X121LF	E	8	6	6	6	6	6
	D	8	6	6	6	6	6
	C	5	6	6	6	6	6
	B	8	6	6	6	6	6
	A	8	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X125LF	E	6	6	6	6	6	6
	D	6	6	6	6	6	6
	C	20	20	20	20	20	20
	B	6	6	6	6	6	6
	A	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X129LF	E	2	2	2	2	4	4
	D	2	2	2	2	4	4
	C	2	2	2	2	4	2
	B	2	2	2	2	4	4
	A	2	2	2	2	2	1
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X110LF	E	3	2	2	2	2	2
	D	3	2	2	2	2	2
	C	3	2	2	2	2	2
	B	3	2	2	2	2	2
	A	3	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X114LF	E	4	2	3	3	2	4
	D	4	2	3	3	2	4
	C	4	2	3	3	2	4
	B	4	2	3	3	2	4
	A	4	2	3	3	2	4
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X118LF	E	8	6	6	6	6	6
	D	8	6	6	6	6	6
	C	8	6	6	6	6	6
	B	8	6	6	6	6	6
	A	8	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X122LF	E	3	3	3	2	2	2
	D	2	2	2	2	2	2
	C	2	2	2	2	2	2
	B	2	2	2	2	2	2
	A	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X126LF	E	2	2	2	4	2	2
	D	2	2	2	4	2	2
	C	2	2	2	4	2	2
	B	2	2	2	4	2	2
	A	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X130LF	E	2	2	2	2	2	2
	D	4	4	4	4	4	4
	C	4	4	4	4	4	4
	B	4	4	4	4	4	4
	A	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X111LF	E	2	2	2	2	2	3
	D	2	2	2	2	2	3
	C	2	2	2	2	2	3
	B	2	2	2	2	2	3
	A	2	2	2	2	2	3
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X115LF	E	2	2	2	1	2	2
	D	2	2	2	1	2	2
	C	2	2	2	1	2	2
	B	2	2	2	1	2	2
	A	1	2	2	1	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X119LF	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
	C	1	2	2	2	2	2
	B	1	2	2	2	2	2
	A	1	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X123LF	E	2	2	2	2	2	2
	D	2	2	2	2	2	2
	C	19	19	19	19	19	19
	B	2	2	2	2	2	2
	A	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X127LF	E	2	2	4	2	2	2
	D	2	4	4	2	2	2
	C	2	4	4	2	2	2
	B	2	4	4	2	2	2
	A	2	2	4	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X131LF	E	8	6	6	8	6	6
	D	8	6	6	8	6	6
	C	8	8	8	8	5	6
	B	8	6	6	8	6	6
	A	8	6	6	8	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X112LF	E	7	6	6	6	6	6
	D	7	6	6	6	6	6
	C	7	6	6	6	6	6
	B	7	6	6	6	6	6
	A	7	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X116LF	E	5	6	6	6	6	6
	D	5	6	6	6	6	6
	C	5	6	6	6	6	6
	B	5	6	6	6	6	6
	A	5	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X120LF	E	2	2	2	2	2	4
	D	2	2	2	2	2	4
	C	2	2	2	2	2	4
	B	2	2	2	2	2	4
	A	2	2	2	2	2	4
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X124LF	E	2	2	2	1	2	2
	D	2	2	2	2	2	2
	C	2	2	2	2	2	2
	B	2	2	2	2	2	2
	A	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X128LF	E	2	2	2	4	2	2
	D	2	2	2	4	2	2
	C	2	2	2	4	2	2
	B	2	2	2	4	2	2
	A	2	2	2	4	2	2
METRAL P/N	ROW	CONTACT CODE MOD. I					
		1	2	3	4	5	6
		1	2	3	4	5	6
89006-X132LF	E	8	6	7	6	6	6
	D	8	6	7	6	6	6
	C	5	6	6	8	6	6
	B	8	8	7	8	6	6
	A	8	8	7	8	6	6

spec ref		*		dr	Terran Huang	2010/07/08	projection 	mm 	size	A4	scale	1:1					
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng			Narayanan, Aru	2018/05/18	ecn no			ELX-I-30208-1			
ISO 406 ISO 1101						chr			-	-	rel level				Released		
				appr	K-Paul Biju	2018/05/20	product family		METRAL								
surface			linear	0.X	±0.3	Amphenol FCI		title	METRAL SIGNAL HEADER				dwg no	89006		rev	BK
				0.XX	±0.13												
				0.XXX	±.050												
ISO 1302		angular	0°	±2°	www.fci.com		cat. no.	-	Product - Customer Drw				sheet 7 of 9				



PRODUCT NUMBER

89006-XYLFF

NOTES:

1. FOR DIM A AND B SEE SHEET 2 AND UP.

2. BODY MATERIAL: LIQUID CRYSTAL

POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.3. PIN MATERIAL:
PHOSPHOR BRONZE.

4. PLATING ON PRESS-FIT TAIL:

73931-XYLFF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE BELOW.5. PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.6. ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP7. PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073⑧ AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.⑨ THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-47-0004.ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

10. -A PLATING HAS Au FLASH IN PRESS FIT AREA (LEAD FREE)

⑪ A Δ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

PLATING IN CONTACT AREA		
DASH NUMBER	PERFORMANCE LEVEL	NOTES
-N1YY	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-N5YYLF	TELCORDIA UE (NXT)	SEE NOTE 9
-1YYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YYLF	TELECOM CLASS	SEE NOTE 9
-5YYLF	TELCORDIA UE	SEE NOTE 9

spec ref		*		dr	Terran Huang	2010/07/08	projection	mm	size	A4	scale	1:1										
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Narayanan, Aru	2018/05/18			ecn no	ELX-I-30208-1												
ISO 406				chr	-	-																
ISO 1101				appr	K-Paul Biju	2018/05/20			product family		METRAL		rel level	Released								
surface			linear	0.X	±0.3		Amphenol FCI			title			METRAL SIGNAL HEADER		dwg no		89006		rev		BK	
			0.XX	±0.13																		
			0.XXX	±.050																		
ISO 1302		angular	0°	±2°		www.fci.com		cat. no.		-		Product - Customer Drw				sheet 9 of 9						