



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/7/11	D.GRIFFIN

DC POWER JACK



2X TYPE N
FEMALE CONNECTOR

RoHS Compliant ✓

NOTES:

1. AMPLIFIER DESIGNED FOR INDOOR USE ONLY.
2. EACH UNIT TO BE INDIVIDUALLY PACKAGED PER L-COM SPECIFICATIONS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. CASTRO	4/6/11		
	CHECKED BY K. BURGNER	4/6/11	CATEGORY	AMPLIFIERS
	APPROVED BY K. BURGNER	4/6/11	PRODUCT DESCRIPTION	2.4 GHz MG SERIES INDOOR AMPLIFIER
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. HA2401MG
	SCALE: NONE	CAD FILE: HA2401MG.SLDDRW	SHEET 1 OF 1	