






| MATERIAL NUMBER | OLD PART NUMBER |
|-----------------|-----------------|
| 130060-0065     | DNAUX4000       |



FEMALE FACE VIEW



MALE FACE VIEW

CENELEC EN 50 044 PINOUT SHOWN  
(SAE-J-1738A PINOUT SHOWN IN PARENTHESIS)

|                       |             |
|-----------------------|-------------|
| VOLTAGE RATING        | 600 VAC/VDC |
| AMPERAGE RATING       | 10 AMPS     |
| PROTECTION            | IP67        |
| OPERATING TEMPERATURE | 0°C TO 60°C |

| ITEM | COMPONENT        | MATERIAL      | FINISH           |
|------|------------------|---------------|------------------|
| 1    | INSERT           | PVC           | YELLOW           |
| 2    | CONTACT SOCKET   | COPPER ALLOY  | GOLD OVER NICKEL |
| 3    | CONTACT PIN      | COPPER ALLOY  | GOLD OVER NICKEL |
| 4    | RECEPTACLE SHELL | ZINC DIE CAST | BLACK E-COATED   |
| 5    | HOUSING          | PBT           | YELLOW           |
| 6    | LABEL            | ABS           | WHITE            |
|      | POTTING MATERIAL | EPOXY         | TRANSLUCENT      |

|                                                                                                                    |             |
|--------------------------------------------------------------------------------------------------------------------|-------------|
| INITIAL RELEASE<br>EC NO: WNA2010-0453<br>DRWN: KJOZWIK 2010/01/25<br>CH'KD: BWOODMAN<br>APPR: JFMURPHY 2010/01/29 | DESCRIPTION |
| A                                                                                                                  | REV         |

| QUALITY SYMBOL |
|----------------|
| ▽=0            |
| ▽=0            |

| GENERAL TOLERANCES (UNLESS SPECIFIED)                   |       |       |
|---------------------------------------------------------|-------|-------|
|                                                         | mm    | INCH  |
| 4 PLACES                                                | ±---  | ±---  |
| 3 PLACES                                                | ±---  | ±---  |
| 2 PLACES                                                | ±0.13 | ±.010 |
| 1 PLACE                                                 | ±0.25 | ±.020 |
| ANGULAR ±1/2°                                           |       |       |
| DRAFT WHERE APPLICABLE<br>MUST REMAIN WITHIN DIMENSIONS |       |       |

| DIMENSION STYLE |            |
|-----------------|------------|
| IN/MM           |            |
| DRAWN BY        | DATE       |
| KJOZWIK         | 2010/01/25 |
| CHECKED BY      | DATE       |
| BWOODMAN        | 2010/01/25 |
| APPROVED BY     | DATE       |
| JFMURPHY        | 2010/01/29 |
| MATERIAL NO.    |            |
| SEE CHART       |            |
| SIZE            |            |
| C               |            |

|                                                                                                        |                      |                                                                                       |                           |
|--------------------------------------------------------------------------------------------------------|----------------------|---------------------------------------------------------------------------------------|---------------------------|
| SCALE<br>1:1                                                                                           | DESIGN UNITS<br>INCH |  | THIRD ANGLE<br>PROJECTION |
| TITLE                                                                                                  |                      |                                                                                       |                           |
| MINI 4 PORT DROP MPIS<br>DEVICENET AUX POWER<br>----                                                   |                      |                                                                                       |                           |
|                   | MOLEX INCORPORATED   |                                                                                       |                           |
| DOCUMENT NO.<br>SD-130060-010                                                                          |                      |                                                                                       | SHEET NO.<br>1 OF 1       |
| CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                      |                                                                                       |                           |