




P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PRELIMINARY DRAWING	20MAY2016	AD	SH


1. MATERIAL : CAGE :0.3MM THICK NICKEL SILVER ALLOY;
EMI SPRING: COPPER ALLOY;
2. FINISH: EMI SPRING -1.27um NICKEL PALTING OVER ALL;
- 3.MATES WITH CFP MSA COMPLIANT TRANSCEIVERS.
- 4.DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 5.MINIMUM PC BOARD THICKNESS: SIGLE SIDE APPLICATIONS=2.99±0.10mm.
BELLY TO BELLY APPLICATION 3.0mm MIN.
- 6.PADS AND VIAS CHASSIS GROUND;
- 7:REFERENCE APPLICATION SPEC 114-XXXX,HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 8DATE CODE MARKED APPROXIMATE AREA





THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

2288227-2
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY.XIF 20MAY2016	 TE Connectivity	
DIMENSIONS:		CHK SEAN.HAN 20MAY2016		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SEAN.HAN 20MAY2016		
mm		PRODUCT SPEC		
0 PLC ±		-	NAME	
1 PLC ±0.25		-	CAGE ASSEMBLY, CFP4 1X1	
2 PLC ±0.15		-	PRESS FIT, EMI SPRING	
3 PLC ±0.1		-	SIZE	
4 PLC ±		-	CAGE CODE	
ANGLES ±		-	DRAWING NO	
FINISH		-	RESTRICTED TO	
MATERIAL		-	A2	
-		-	C-2288227	
-		-	CUSTOMER DRAWING	
		-	SCALE 3:1	
		-	SHEET 1 OF 4	
		-	REV 1	







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY.XIE 20MAY2016	TE Connectivity			
DIMENSIONS: mm		CHK SEAN.HAN 20MAY2016				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SEAN.HAN 20MAY2016	NAME CAGE ASSEMBLY,CFP4 1X1 PRESS FIT,EMI SPRING			
0 PLC ±-		PRODUCT SPEC	SIZE A2			
1 PLC ±0.25		APPLICATION SPEC	CAGE CODE -			
2 PLC ±0.15		WEIGHT	DRAWING NO C-2288227			
3 PLC ±0.10		CUSTOMER DRAWING	RESTRICTED TO -			
4 PLC ±-			SCALE 4:1 SHEET 4 OF 4 REV 1			
ANGLES ±-						
FINISH						
MATERIAL						
-						
-						