NOTES:

I. MATERIAL AND FINISH (PLATING THICKNESS IN MICRO-INCHES): BERYLLIUM COPPER, ALBALOY PLATING OVER SILVER

CONTACT PIN BERYLLIUM COPPER, GOLD PLATING INSULATOR PTFE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE:50 OHM

B. FREQUENCY RANGE: DC- 6 GHz

C. RETURN LOSS(VSWR) AT AXIAL FLOAT POSITION:

DC-3 GHz: 30 dB (1.07) @ NOMINAL 21 dB (1.20) @ \pm 0.7 mm 3-6 GHz: 29 dB (1.07) @ NOMINAL

15 dB (1.43) @ \pm 0.7 mm D. INSULATION RESISTANCE: 5 GOHM MIN.

E. POWER HANDLING: 40 W MAX.@ 2.6GHz AT 85°C

F. 3TH PIM: -150 dBc Max.@ 2100 MHZ (2X43 dBM)

3. MECHANICAL:

A. MATING CYCLES: 200 MIN FOR SMOOTH BORE 50 MIN FOR LIMITED DETENT


B. TEMPERATURE RANGE: -55°C TO +125°C

4. PACKAGING:

A. PACKAGE IN 50 PIECE TRAYS

B. MARK TRAYS: "AMPHENOL RF, 920-506A-51S, DATE CODE"

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: MATERIAL




DRAWN


DATE

TITLE





SCALE 10.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

10.5	IMATERIAL	DIVUIN	DAIL
<0.5mm	OFF WOTEO	B. GREENBAUM	24-May-17
property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they	SEE NOTES	ENGINEER	DATE
	REFERENCE	B. GREENBAUM	24-May-17
are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is	LAK# /563	APPROVED	DATE
not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell	REF: 615X-3350-X00	K.CAPOZZI	24-May-18
	CONFIGURATION LEVEL: In Work	CAD FILE	
	FINISH		

HD-EFI 7.72MM	Amphenol RF
BULLET	www.amphenolrf.com
00415 00 0 1 0 01557 0 05 0	DRAWING NO. 920-506A-51S
SCALE: 20.0:1.0 SHEET 2 OF 2 DWG SIZE REV	ITEM NO. 920-506A-51S
В А	PART NO. 920-506A-51S