


DRAWING MADE IN AMERICAN PROJECTION



RECOMMENDED LAYOUT
FOR .062 THICK P.C. BOARD

TYPE NON-ACCUM.

±.005

±.005

±.003

.070 DIA.

1. PARTS COMPLY WITH TE SOLDERABILITY
SPEC. NO. 109-11-3

△ CONTACT IS PLATED OVERALL WITH .000050 NICKEL, THEN
.000030 GOLD OVER CONTACT LENGTH INDICATED, AND
ITIN PLATED ON SOLDER TAIL END.

SUPERSEDED BY
1586518-2

350212-2	NYLON	NATURAL	COPPER ALLOY	GOLD	△
350212-1	NYLON - NATURAL	Copper Alloy	PRE-TIN		
ASSEMBLY NO.	HGS. MATL. - COLOR	PIN MATL. - FINISH			

Models and copy not to be reproduced without written permission of ETE Incorporated.

P2	REVISED PER ECR-10-009130	JB	DZ	19 JUN 2018
P1	REVISED PER ECR-13-008342	AV	RP	13 NOV 2013
P	OBS 1-1 2-1 9-1 PER ECR CM-2706	NG	RS	8 FEB 1978
N	OBS 5-1 6-1 PER CM 2213	PS	RS	7 FEB 1978
LTR	REVISION RECORD	DR	CHK	DATE

REQUIRED PER ASSEMBLY		NUMBER	NAME	REMARKS	ITEM NO.
DESCRIPTION		© 1978 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING. CUSTOMER COPY REFERENCE ONLY			
DR <i>W. H. H. 3/15/73</i> CHK <i>W. H. H. 3/15/73</i> DE <i>Thibault 4-3-73</i> APP <i>Thibault 4-3-73</i>		MATERIAL AND FINISH SEE TABLE WIRE - RANGE - INSULATION TOLERANCE EXCEPT AS NOTED SCALE LOC NO NAME		CLASS PIN HEADER CM B 350212 P2	

PRINTED AT 53 DIMENSIONS IN INCHES. DO NOT SCALE PRINT.