






REVISIONS					
REV	LTR	DESCRIPTION	DATE	DWN	APPD
	A1	UPDATED PER ECO-17-010992	07MAR2017	RS	MD


SUGGESTED MATING TAB




- MATL: ½ H BRASS OR NICKEL PL STEEL.
 - NO BURRS PERMISSIBLE AT HOLE.
 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F
 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



VIEW C-C
SCALE 8:1



SECTION A-A
SCALE 8:1



SECTION B-B
SCALE 8:1

- DIMENSIONS IN BRACKETS ARE IN INCHES.
- PRODUCT PROVIDED IN STRIP FORM, BREAKS MAY BE PRESENT.
- THIS PART HAS NOT COMPLETED QUALIFICATION TESTING

1.52-2.54 [.060-.100] DIA	#20-#18 AWG	2238141-1
INSULATION RANGE	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: PASVESH WARAD 07MAR2017	TE Connectivity	
		CHK: MIKE DIDONATO 07MAR2017		
DIMENSIONS: mm(INCHES)	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPD: MIKE DIDONATO 07MAR2017	NAME	RECEPTACLE, FLAG, POSITIVE-LOCK, .250 SERIES
	0. PLC ± -	PRODUCT SPEC		
	1. PLC ± -			
	2. PLC ± -			
	3. PLC ± 0.25 [.010]	APPLICATION SPEC		
	4. PLC ± -			
	ANGLES ± -			
MATERIAL -	FINISH -	WEIGHT 0	SIZE A1	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV A1