



INSULATED PHONE TIP PLUGS



- HANDLES:** Molded plastic as indicated in table.
BODY: Brass, Nickel-plated..
COLORS:
 A: Available in Red and Black. Add color number as suffix to part number.
 B: Available in 6 colors. Add color number as suffix to part number.
 -101 White -102 Red -103 Black
 -104 Green -105 Blue -107 Yellow
 C: Available in 10 colors. Add color number as suffix to part number.
 -101 White -102 Red -103 Black -104 Green -105 Blue
 -106 Orange -107 Yellow -108 Brown -112 Violet -113 Gray

PART NO.	ILLUS.	TYPE	HANDLE MATERIAL	COLORS	AMPS	VOLTS
244	A	Min. Solder	ABS	A	2	.600
229	B	Heavy Duty	Nylon		15	1 KV
235	C	RA Solder	ABS		12	
203	D	Solder	Nylon	B	12	
283	E					
491	F	.078 Solder	Polycarbonate	C		
492	G	.154 Solder				
201	H	Solderless	Nylon	B		
200	J					
490	K		Polycarbonate	C		

UNINSULATED PHONE TIP PLUGS



BODY: Brass, Nickel-plated.
NEEDLE TIP: Steel, Nickel-plated.
ASSEMBLY: Force-Fit type press into .240 max. hole in prods. Threaded types fit 1/4-32 internal tap, minimum of 9/32" deep.
WIRING: Wire leads solder into well in back of plug. On solderless types, wire fits through hole in body, wraps around screw portion, and is held with knurled collar.
RATING: 12 Amps AC for 10°C temperature rise, continuous duty.

PART NO.	ILLUS.	TYPE	MOUNTING	STYLE
156	A	Solder	Force Fit	Long, Heavy duty
125	B		Threaded	
106	C	Solderless	Force Fit	Short tip
127	D		Threaded	Short tip
105	E		Force Fit	Long tip
124	F		Threaded	Long tip
128	G	Solder	Threaded	Replaceable needle tip
108	H		Wire Mnt.	Earphone tip, machined
123	J		Wire Mnt.	Earphone tip, large ID