








THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	3/11/10	D.GRIFFIN
B	ECN 8473 - UPD DWG TO MATCH NEW DESIGN. ADD MATERIAL & NOTE 4 INFC	09/20/14	D.CUI
C	ECN 8514: ADD NOTES 5	10/20/16	D.CUI
D	ECN 9117: REMOVED NUT GATE	03/23/18	D.CUI



PART NUMBER	LENGTH	
	METERS	FEET
WPUSBAXSH-05M	0.5	1.64
WPUSBAXSH-1M	1.0	3.28
WPUSBAXSH-2M	2.0	6.56
WPUSBAXSH-3M	3.0	9.84
WPUSBAXSH-5M	5.0	16.40

- NOTES:
1. THESE CABLE ASSEMBLIES ARE CONSTRUCTED TO MEET THE REQUIREMENTS OF THE UNIVERSAL SERIES BUS SPECIFICATION USB 2.0
  2. CONNECTOR CONTACTS HAVE 30 MICROINCHES GOLD PLATING OVER NICKEL PLATING.
  3. INGRESS PROTECTION RATING IS IP67 (J1 ONLY, MATED)
  4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  5. L-COM LOGO STYLE AND MOLDED HOOD APPEARANCE MAY VARY PER L-COM SPECIFICATION
  6. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.



RECOMMENDED PANEL OPENING

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm)	
OVERALL CABLE LENGTH TOLERANCE:	
<math>\le 12 [305]</math>	$\pm 1 [25] / -0$
<math>> 12 [305]</math>	$\pm 2 [51] / -0$
<math>> 60 [1524]</math>	$\pm 3 [76.2] / -0$
<math>> 120 [3048]</math>	$\pm 5 [127] / -0$
<math>> 300 [7620]</math>	$\pm 8 [203] / -0$
ALL OTHER DIMENSIONAL TOLERANCES:	
X	$\pm 2 [50.8]$
XX	$\pm 1 [25.4]$
XXX	$\pm .005 [127]$

APPROVALS		DATE
DRAWN BY	D. CASTRO	2/1/10
CHECKED BY	D. PARHAM	2/1/10
APPROVED BY	S. SMITH	2/1/10



CATEGORY	USB		
PRODUCT DESCRIPTION	CA IP67 USB-A-F/A-M SHLD		
SIZE	FSCM NO.	DWG. NO.	REV.
B	43321	WPUSBAXSH	D
SCALE: 1:1	CAD FILE: WPUSBAXSH.DDDRW	SHEET 1 OF 1	

REGULATORY COMPLIANCE:  
CE2011/65/EU (RoHS DIRECTIVE)