







Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.




CODE NO.	CONTACT	A	B	C	D	E	F	G	H	J
CL683-0042-7-57	20	10	6.8	5.5	4.5	9.8	8.2	7	10.4	7.6
CL683-0043-0-57	30	12.5	9.3	8	7	12.3	10.7	9.5	12.9	10.1
CL683-0044-2-57	40	15	11.8	10.5	9.5	14.8	13.2	12	15.4	12.6
CL683-0045-5-57	50	17.5	14.3	13	12	17.3	15.7	14.5	17.9	15.1
CL683-0046-8-57	60	20	16.8	15.5	14.5	19.8	18.2	17	20.4	17.6
CL683-0047-0-57	70	22.5	19.3	18	17	22.3	20.7	19.5	22.9	20.1
CL683-0048-3-57	80	25	21.8	20.5	19.5	24.8	23.2	22	25.4	22.6

NOTES 1 LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.
2 WATCH NOT LET THE CONTACTS TOUCH THE SECTION ESPECIALLY WHEN THE PADS OF AREA NOT RESIST FINISHED.


MATED HEIGHT(h)		(mm)
RECEPTACLE NO.	HEADER NO.	
DF17#(4.0)-*DS-0.5V(57)		
DF17#(2.0)-*DP-0.5V(57)	6	
DF17#(4.0)-*DP-0.5V(57)	8	




2		POLYAMIDE (PA6T)	WHITE BEIGE , UL94V-0	6	PS	BLACK(PLASTIC REEL)			
1		PHOSPHER BRONZE	CONTACT AREA : GOLD PLATED 0.1μm min LEAD AREA : TIN PLATED 1μm min UNDER PLATING : NICKEL PLATED 1μm min	5	POLYESTER	CLEAR (COVER TAPE)			
				4	PS	CLEAR (EMBOSSED CARRIER TAPE)			
				3	PHOSPHER BRONZE	TIN PLATED : 1μm min UNDER PLATING : NICKEL PLATED 1μm min			
NO.	MATERIAL		FINISH , REMARKS	NO.	MATERIAL		FINISH , REMARKS		
UNITS mm			SCALE 5 : 1	COUNT 	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.			APPROVED : KH. IKEDA	11. 11. 30	DRAWING NO. EDC3-162131-77				
			CHECKED : TS. MIYAZAKI	11. 11. 30	PART NO. DF17(4. 0)- *DS-0. 5V(57)				
			DESIGNED : YH. MICHIDA	11. 11. 30	CODE NO. CL683				
			DRAWN : YH. MICHIDA	11. 11. 30	 1/2				



CODE NO.	CONTACT	L	M	N	P	Q
CL683-0042-7-57	20	24	—	11.5	10.3	25.5
CL683-0043-0-57	30	24	—	11.5	12.8	25.5
CL683-0044-2-57	40	24	—	11.5	15.3	25.5
CL683-0045-5-57	50	32	28.4	14.2	17.8	33.5
CL683-0046-8-57	60	32	28.4	14.2	20.3	33.5
CL683-0047-0-57	70	44	40.4	20.2	22.8	45.5
CL683-0048-3-57	80	44	40.4	20.2	25.3	45.5


$$R-R$$

STYLE AND DIMENSION OF REEL (FREE)



SUPPLIER
QUANTITY
PART NO.
CODE NO.
DATE OF MANUFACTURED

DETAIL OF PART NO. LABEL	
生産月日	年 月 日
図番	CL683-****-*-57
品名	DF17(4.0)-*DS-0.5V(57)
納入数量	1000K0
納入者	ヒコセ電機(株)

3. 1 REEL : 1000 CONNECTORS.
4. AT THE BEGINNING OF THE REEL , 30 COMPONENTS SHALL BE EMPTY.
AT THE END OF THE REEL, 20 COMPONENTS SHALL BE EMPTY.
5. WHEN THE TAPE WIDTH IS 32mm or 44mm, SPROCKET HOLES SHALL BE SET ON BOTH SIDES OF REEL AS SHOWN ON THIS DRAWING.
6. PEEL FORCE REFERS TO JIS C 0806.
7. A POCKET SHAPE IS DIFFERENT AT INTERVALS OF EACH CAVITY NUMBER TO AVOID OVERLAP.

HRS	DRAWING No.	EDC3-162131-77		
	PART No.	DF17(4.0)-*DS-0.5V(57)		
	CODE No.	CL683		$\frac{2}{2}$