



REVISIONS				
REV	DATE	DESCRIPTION	BY	CHKD
D	26MAR2018	REV PER ECO-18-004564	MY	GF
E	24APR2018	REV PER ECO-18-005973	MY	GF
F	17JUL2018	REV PER ECO-18-005973	MY	GF



1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFRENTIALLY)

△ LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -6): -1 SHOWN




3. SEE SHEET 2 FOR WIRING SCHEMATIC.

4. ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY SPECIFICATION TEC-138-702.

△ TEST IN ACCORDANCE WITH IEEE802.3by.

△ DUE TO SHORT CABLE LENGTH, THE PART NUMBERS INDICATED MAY NOT MEET IEEE802.3by RETURN LOSS AND MINIMUM INSERTION LOSS LIMITS.

△ LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -45): -41 SHOWN




△ DASH NUMBER 41 THRU 45 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

△ 8	30 AWG	2000 +80/-0	4-2821222-5
	30 AWG	1500 +80/-0	4-2821222-4
	30 AWG	1000 +50/-0	4-2821222-3
	30 AWG	750 +50/-0	4-2821222-2
	30 AWG	500 +50/-0	4-2821222-1
△ 5	30 AWG	2500 +80/-0	2821222-6
	30 AWG	△ 500 +50/-0	2821222-5
	30 AWG	1500 +80/-0	2821222-4
	30 AWG	1000 +50/-0	2821222-3
	30 AWG	2000 +80/-0	2821222-2
	30 AWG	3000 +80/-0	2821222-1
STANDARD	WIRE GAGE	L	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: T. SMITH 11APR2017	CHK: E. CUESTA 11APR2017	APVD: E. CUESTA 11APR2017
mm	0 PLC ±	TE Connectivity NAME: CABLE ASSEMBLY, 30 AWG, SFP+ TO SFP+ 28G PRODUCT SPEC: - APPLICATION SPEC: - SIZE: A1 CAGE CODE: - DRAWING NO: C=2821222 RESTRICTED TO: - WEIGHT: - CUSTOMER DRAWING: -		
	1 PLC ±			
	2 PLC ±			
	3 PLC ±			
	4 PLC ±	SCALE: 8:1	SHEET: 1 OF 2	REV: F
MATERIAL:	FINISH:			

REVISIONS				
P.	LTN	DESCRIPTION	DATE	OWN APVD
		SEE SHEET 1		



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN T. SMITH 11APR2017	
DIMENSIONS: mm		CHK E. CUESTA 11APR2017	
		APVD E. CUESTA 11APR2017	NAME CABLE ASSEMBLY, 30 AWG, SFP+ TO SFP+ 28G
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE A1
0 PLC ±		APPLICATION SPEC	CAGE CODE -
1 PLC ±		WEIGHT	DRAWING NO C=2821222
2 PLC ±		CUSTOMER DRAWING	RESTRICTED TO
3 PLC ±		SCALE 8:1	SHEET 2 OF 2
4 PLC ±		SCALE	REV F
ANGLES ±			
FINISH			