


Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.

COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△	1	DIS-C-000490	T.H.E.k		07.01.31	△					
△						△					
△						△					




- NOTES
- ① TOTAL LENGTH BECOMES 37.3±1 WHEN ⑥ IS SCREWED INTO ① COMPLETELY.
 - ② APPLICABLE CRIMPING CONTACT:HR30-PC-211
(APPLICABLE WIRE:26-30 AWG WIRE JACKET DIAMETER:φ1 MAX)
APPLICABLE CONTACT WITHDRAWAL HP30-TP
 - ③ THE RECOMMENDED CLUMP TORQUE OF REF. NO.⑥ TO BE 0.5N·m.
SPACER FOR ASSEMBLY IS AVAILABLE HR30-8P-T02.
STAND FOR ASSEMBLY IS AVAILABLE HR30-7J-12PC-T01.
 - △④ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

3	PBT	(BLACK)	UL94V-0	6	PPS	(BLACK)	UL94V-0
2	PPS	(BLACK)	UL94V-0	5	SYNTHETIC RUBBER	(BLACK)	
1	PPS	(BLACK)	UL94V-0	4	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	

CODE NO.(OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		E.KUNII	E.KUNII		M.SATO	
		'05.10.14	'05.10.14		'05.10.17	

SCALE 5 : 1 UNITS mm	DRAWING NO. EDC3-112268-71		PART NO. HR30-7J-12PC(71)	
	HRS HIROSE ELECTRIC CO., LTD		CODE NO. CL130-2017-4-71	
			1/1	

LIFE SIZE(1 : 1)



TO
R
F