



- NOTES
- ① PLATING (REF. NO. ③)
SURFACE PLATING : GOLD 0.2 μm min.
UNDER PLATING : NICKEL 2 μm min.
 - ② THE RECOMMENDED CLAMP TORQUE OF REF. NO. ① IS RECOMMENDED TO PREVENT REF. NO. ⑦ FROM LOOSING.
RECOMMENDED TREAD LOCKER : LOCTITE 271, HENKEL JAPAN LTD.
 - ③ WHEN THIS CONNECTOR IS MOUNTED ON TO PANEL, BE CAREFUL REF. NO. ⑤ IS ASSEMBLED SURELY INTO THE GROOVE OF REF. NO. ⑤ AS SHOWN IN THIS FIGURE TO KEEP WATERPROOF EFFECTIVENESS.
 - ④ CORRESPONDING CONNECTOR : LF10WBP*-12S
DO NOT MATE LF10WBRB-12PD TO LF10WBP*-12P(※※)
IT MAY CAUSE FAILURE SUCH AS CONTACT COMING OFF AND / OR CONNECTOR DEFORMATION.
(* IS REPLACED BY AN ALPHABET SUCH AS A, B, . . . , OTHERWISE DELETED.)
(※※ IS REPLACED BY AN 2 NUMERICAL DIGITS WHEN THERE IS A SPECIFICATION CHANGE.)

4	PHOSPHOR BRONZE	NICKEL PLATING			
3	COPPER ALLOY	①	7	BRASS	NICKEL PLATING
2	PPS	(BLACK) UL94V-0	6	PHOSPHOR BRONZE	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	5	CHLOROPRENE RUBBER	(BLACK)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 4 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-002180	DESIGNED HK. NAMAI
		APPROVED : SU. OBARA	09.10.27	DRAWING NO. EDC3-116626-00	
		CHECKED : HY. KISHI	09.10.27	PART NO. LF10WBRB-12PD	
		DESIGNED : TY. SUZUKI	09.10.26	CODE NO. CL136-1015-1-00	
		DRAWN : TY. SUZUKI	09.10.26		
				DATE 11.05.13	