









CODE NO.	CONTACT	A	B	C	D	E	F	G
CL537-0053-4-86	20	7.2	4.5	5.3	5.7	6.6	5.3	8.1
CL537-0055-0-86	30	9.7	7.0	7.8	8.2	9.1	7.8	10.6
CL537-0926-2-86	32	10.2	7.5	8.3	8.7	9.6	8.3	11.1
CL537-0056-2-86	36	11.2	8.5	9.3	9.7	10.6	9.3	12.1
CL537-0057-5-86	40	12.2	9.5	10.3	10.7	11.6	10.3	13.1
CL537-0059-0-86	50	14.7	12.0	12.8	13.2	14.1	12.8	15.6
CL537-0061-2-86	60	17.2	14.5	15.3	15.7	16.6	15.3	18.1




NOTES 1 LEAD CO-PLANARITY INCLUDING REINFORCED METAL FITTINGS SHALL BE 0.08 mm MAX.

② IF THERE IS PATTERN ON  PART, THERE IS A POSSIBILITY THAT IT WILL MAKE CONTACT WITH THE LEADS.

3 REINFORCED METAL FITTINGS AS FOLLOWS.



2	PHOSPHOR BRONZE	CONTACT AREA:GOLD PLATED 0.2#m min	5	POLYESTER	CLEAR(COVER TAPE)
		LEAD AREA:GOLD PLATED 0.015#m min	4	PS	CLEAR(EMBOSSSED CARRIER TAPE)
		OTHERS(UNDER PLATING):NICKEL 2#m min	3	BRASS	TIN PLATED 2#m min UNDER PLATING:NICKEL 1#m min
1	POLYAMIDE	BEIGE. UL94V-0			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 5 : 1	 COUNT 1	DESCRIPTION OF REVISIONS DIS-H-00001707	DESIGNED SH. HOSODA	CHECKED TS. MIYAZAKI	DATE 16. 06. 10
 HIROSE ELECTRIC CO., LTD.		APPROVED +KH. IKEDA	13. 08. 19	DRAWING NO.	EDC3-162870-77		
		CHECED +YH. MICHIDA	13. 08. 09	PART NO.	DF12(4. 0)-*DP-0. 5V(86)		
		DESIGNED +YN. SAKAMOTO	13. 08. 08	CODE NO.	CL537		
		DRAWN +KR. AJITO	13. 08. 08				

