


Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case that the application demands a high level of reliability, such as automotive,  
 please contact a company representative for further information.

1		2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△					△					
△					△					
△					△					



- 1 ROTATION EXAMPLES OF REF.NO. ① AND ⑧ ARE SHOWN.
- 2 THE RECOMMENDED TORQUE OF REF.NO. ⑧ : 2 TO 3N · m.
- 3 THE RECOMMENDED TORQUE OF REF.NO. ⑪ : 0.3 TO 0.4N · m.
- 4 BOLTING TOOL FOR REF.NO. ⑪ : PB205/1.27(CL150-0066-3)

11	STEEL	NICKEL PLATING	THE WIDTH ACROSS OF A HEXAGON SOCKET: 1.27
10	BRASS	NICKEL PLATING	
9	ZINC ALLOY	MATTE FINISH NICKEL PLATING	
8	ZINC ALLOY	MATTE FINISH NICKEL PLATING	
7	BRASS	NICKEL PLATING	
6	BERYLLIUM COPPER	NICKEL PLATING	
5	BRASS	MATTE FINISH NICKEL PLATING	
NO.	MATERIAL	FINISH, REMARKS	

4	DIALLYL PHTHALATE	(BLACK) UL94V-0
3	DIALLYL PHTHALATE	(BLACK) UL94V-0
2	COPPER ALLOY	SILVER PLATING 2μ m min.
1	ZINC ALLOY	MATTE FINISH NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)	CL	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		E. Yumino	y. Yamadori	H. Zemba	M. Sato	
		05.11.28	05.11.28	05.11.30	05.11.30	

SCALE	DRAWING NO.	PART NO.
2 : 1	EDC4-112319-71	RM12BPE-2PH(71)
UNITS	CODE NO.	
mm	CL109-0417-7-71	1/1

TO  
 R