







APPLICATION DIAGRAM



RECOMMENDED PATTERN(5:1)
(RECOMMENDED BOARD THICKNESS t=1.6mm)



NOTES 1 :IMMERSION DEPTH INTO POTTING SOLUTION:6.5mm


△ 2 :FORCEFULLY UNMATING THE CONNECTORS WILL RISK DAMAGING THEM; THEREFORE,WHEN IT IS DIFFICULT TO UNMATE A CONNECTOR,FIRST GENTLY PRESS DOWN ON IT,THEN RELEASE THE LOCK TO ALLOW REMOVAL.

			3	HIPS	TRAY
			2	BRASS	SURFACE:TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 0.5μm min
1	PBT	WHITE, UL94V-0			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-H-008766	DESIGNED HT. SATO
			CHECKED TS. FUKUSHIMA		
			DATE 14. 05. 19		
			DRAWING NO. EDC3-338420-01		
			PART NO. DF33C-2P-3.3DSA(24)		
			CODE NO. CL676-1131-2-24		
			1/2		

HRS HIROSE
ELECTRIC
CO., LTD.

APPROVED : KI. AKIYAMA 12. 07. 24
CHECKED : HK. UMEHARA 12. 07. 24
DESIGNED : HT. SATO 12. 07. 24
DRAWN : MI. SAKIMURA 12. 07. 23

Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.



△ NOTES 3 :MINIMUM UNIT OF PURCHASE SHALL BE THE QUANTITY
OF CONNECTORS IN TRAY.(135 PIECES)

HRS	DRAWING NO.	EDC3-338420-01	
	PART NO.	DF33C-2P-3. 3DSA(24)	
	CODE NO.	CL676-1131-2-24	△ 2/2