


Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.

1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE			COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE		
△										△									
△										△									
△										△									



- NOTE
- 1 ROTATION EXAMPLES OF REF.NO. ① AND ⑧ ARE SHOWN.
 - 2 THE RECOMMENDED TORQUE OF REF.NO. ⑧: 2 TO 3N · m.
 - 3 THE RECOMMENDED TORQUE OF REF.NO. ⑪: 0.3 TO 0.4N · m.
 - 4 BOLTING TOOL FOR REF.NO. ⑪: PB205/1.27(CL150-0066-3)

11	STEEL	NICKEL PLATING	THE WIDTH ACROSS OF A HEXAGON SOCKET: 1.27
10	BRASS	NICKEL PLATING	
9	ZINC ALLOY	MATTE FINISH NICKEL PLATING	
8	ZINC ALLOY	MATTE FINISH NICKEL PLATING	
7	BRASS	NICKEL PLATING	
6	BERYLLIUM COPPER	NICKEL PLATING	
5	BRASS	MATTE FINISH NICKEL PLATING	

4	DIALYL PHTHALATE	(BLACK) UL94V-0
3	DIALYL PHTHALATE	(BLACK) UL94V-0
2	COPPER ALLOY	SILVER PLATING 2μm min
1	ZINC ALLOY	MATTE FINISH NICKEL PLATING

CODE NO. (OLD) CL		DRAWN Y. Yamada 05.08.26	DESIGNED Y. Yamada 05.08.26	CHECKED H. Zemba 05.08.30	APPROVED M. Sato 05.09.01	RELEASED
DRAWING NO. EDC4-112321-71		PART NO. RM12BPE-4PH(71)				
SCALE 2 : 1		CODE NO. CL109-0419-2-71				1/1
UNITS mm		HIROSE ELECTRIC CO., LTD.				

TO
R