








PART NUMBER	GRNDBAR 1 POS	GRNDBAR 2 POS	GRNDBAR 3 POS	GRNDBAR 4 POS	GRNDBAR 5 POS	GRNDBAR 6 POS	GRNDBAR 7 POS	GRNDBAR 8 POS	GRNDBAR 9 POS	GRNDBAR 10 POS
10127112-101LF	2A,3B,2C,3D,2E	5A,4B,5C,4D,5E	6A,7B,6C,7D,6E	9A,8B,9C,8D,9E	10A,11B,10C,11D,10E	16A,17B,16C,17D,16E	19A,18B,19C,18D,19E	20A,21B,20C,21D,20E	23A,22B,23C,22D,23E	24A,25B,24C,25D,24E
10127112-102LF	2A,3B,2C,3D,2E	5A,4B,5C,4D,5E	6A,7B,6C,7D,6E	9A,8B,9C,8D,9E	10A,11B,10C,11D,10E	NIL	NIL	NIL	NIL	NIL

ABOVE TABLE SHOWS CONNECTED GROUND POSITIONS OF INDIVIDUAL GROUNDBARS

PINNING CONFIGURATION

Z A B C D E F	G	G	G	G	G	G	G	G	G	G		G	G	G	G	G	G	G	G	G	G		
	G	G	HS	HS	G	G	HS	HS	G	G	LS		G	G	HS	HS	G	G	HS	HS	G	G	LS
	HS	HS	G	G	HS	HS	G	G	HS	HS	G		HS	HS	G	G	HS	HS	G	G	LS		
	G	G	HS	HS	G	G	HS	HS	G	G	LS		G	G	HS	HS	G	G	HS	HS	G	LS	
	HS	HS	G	G	HS	HS	G	G	HS	HS	G		HS	HS	G	G	HS	HS	G	G	LS		
	G	G	HS	HS	G	G	HS	HS	G	G	LS		G	G	HS	HS	G	G	HS	HS	G	LS	
	0	0	0	0	0	0	0	0	0	0	0		0	0	0	0	0	0	0	0	0	0	
01								11				15								25			

HS	HIGH SPEED SIGNAL
LS	LOW SPEED SIGNAL
G	GROUND
0	EMPTY



DETAIL A
SCALE 10:1

spec ref		-		dr		Binesh C		2016/02/17		projection		MM		size		A3		scale		2:1	
tolerance std		ISO 406 ISO 1101		eng		Binesh C		2018/06/21						ecn no		ELX-I-30401-1					
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr		-		-		rel level						Released							
				appr		K-Paul Biju		2018/06/21		product family		MILLIPACS									
surface 		linear		0.X		±0.30		Amphenol FCi		title		TYPE A RECEPTACLE ASSEMBLY MILLIPACS HS		dwg no		10127112		rev		C	
				0.XX		±0.20															
				0.XXX		±0.15															
		ISO 1302		angular		0°		±3°				cat. no.		Product - Customer Drw		sheet 1 of 2					

