


| ITEM | MOLEX P/N | DESCRIPTION | QTY | UOM |
|------|-----------|--|-----|-----|
| A,B | 511631200 | 2.5 W/B REC HSG | 2 | PC |
| C | 511641205 | 2.5 W/B RETAINER | 2 | PC |
| D | 507528200 | Mini-Lock2.5 W/B Crimp Rec Term 20-22AWG | 24 | PC |
| E | 884260070 | PAPER PRINTED PAPER WHITE (S100X150YAJ) | 1 | PC |

| FROM | TO | CABLE DESCRIPTION | COLOR |
|------|-----|-----------------------------------|-------|
| A1 | B12 | 20 AWG UL1061 BLACK DISCRETE WIRE | BLACK |
| A2 | B11 | | |
| A3 | B10 | | |
| A4 | B9 | | |
| A5 | B8 | | |
| A6 | B7 | | |
| A7 | B6 | | |
| A8 | B5 | | |
| A9 | B4 | | |
| A10 | B3 | | |
| A11 | B2 | | |
| A12 | B1 | | |



NOTES

1. Cable assembly to be tested 100% for continuity and polarity.
2. Label text must be 2mm max. In height with Arial font.
3. Connector view shown is from mating side.

P/N:151371203 — MOLEX PN
 MOLEX
 BATCH WK/YR

DETAIL A

PENDING APPROVAL

| DATE | REV | DESCRIPTION | REVISED BY |
|------------|-----|--|--------------|
| 2018.05.29 | A | INITIAL RELEASE | SSHIVASHANKA |
| 2018.11.14 | B | CABLE SIZE CHANGED FROM 22AWG TO 20AWG | SSHIVASHANKA |

| | | | |
|---|--|--|--|
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | molex | |
| CURRENT REV DESC: EC NO: 608031 DRWN: SSHIVASHANKA 2018/11/14 CHK'D: APPR: | | MINI-LOCK 12 CIRCUIT 300MM | |
| INITIAL REVISION: DRWN: SSHIVASHANKA 2018/05/29 APPR: MNARAYAN01 2018/06/05 | | PRODUCT CUSTOMER DRAWING | |
| DIMENSION UNITS: mm SCALE: NTS GENERAL TOLERANCES (UNLESS SPECIFIED): ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | DOCUMENT NUMBER: 151371203 DOC TYPE: PSD DOC PART: 000 REVISION: B | |
| SYMBOLS: ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 | | MATERIAL NUMBER: 151371203 CUSTOMER: GENERAL MARKET SHEET NUMBER: 1 OF 1 | |

| | | |
|-----------------|----|--------------|
| DOCUMENT STATUS | RQ | RELEASE DATE |
|-----------------|----|--------------|