



LOC	DIST	REVISIONS					
DF	DO	P	LTR	DESCRIPTION	DATE	OWN	APVD
			J	REVISED PER ECO-13-011791	22AUG13	MGM	CT




FOR (-2, -4 & -7) MARK
MFG'S NAME, BRAND OR LOGO
AND DATE CODE FAR SIDE.
CUSTOMER P/N MARKED NEAR SIDE



FOR (-1 & -11) CUSTOMER P/N MARKED
ON FAR SIDE.
MANUFACTURER'S NAME, BRAND OR LOGO
AND MANUFACTURER'S PART NO AND
DATE CODE MARKED ON NEAR SIDE.
FOR(-2, -4 & -7) MARK MFG'S P/N
FAR SIDE.

—INSERT ASSEMBLY
MATL: DIALLYL PHTHALATE,TYPE SDG—F
PER MIL—M—14,
COLOR: BLUE
OR POLYPHENYLENE SULFIDE (PPS)
PER MIL—M—24519, TYPE GST—40F
COLOR: BLACK


—GROMMET
MATL: SILICONE RUBBER



—SHELL, FRONT & REAR
MAT'L: BRASS PER ASTM B-19
FINISH: .0000050 MIN GOLD PLATED PER
ASTM-B-488 OVER 0.000100
MIN COPPER PER AMS 2418

206071-1 $\triangle 5$

	.120 [3.05]	1B01-029RHW	211671-1	1-211671-1
	.120 [3.05]	B010648-0010	211671-7	211671-7
NOT RELEASED	—	—	211671-6	211671-6
NOT RELEASED	—	—	211671-5	211671-5
	.120 [3.05]	—	211671-4	211671-4
NOT RELEASED	—	—	211671-3	211671-3

DIA A		CUSTOMER P/N ON CONNECTOR		MFG'S P/N ON CONNECTOR		MFG'S P/N	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN CHK J.A. BAKER — APVD —			
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 (0.13) 4 PLC ± — ANGLES ± '0'30' FINISH		NAME CRPT. ASS'Y, AMPLIMITE, 78 POSN, SIZE 5, SERIES 90, NON MAGNETIC WITH GROMMET		 TE Connectivity	
MATERIAL SEE CALLOUTS		WEIGHT —		SIZE A1		CAGE CODE 00779	
SEE CALLOUTS		SEE CALLOUTS		DRAWING NO C-211671		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 1 REV. —	