





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A3	REVISED PER ECR-18-016088	15OCT2018	BW	GJ



POS.	DIM.A	DIM.B
2*6	39.70	37.5
2*5	33.70	31.5
2*4	27.70	25.5
2*3	21.70	19.5




NOTE
 MATERIAL:
 LEVEL 1: NYLON, HIGH TEMPERATURE 150°C
 COLOR: BLACK
 LEVEL 2: PBT GLASS FILLED, HWT. RATED 105°C. RECOMMENDED
 FOR USE WITH HOT WIRE HOUSINGS.
 COLOR: NATURAL


2. MATING CONN, P/N
CAP HSG: *-1971*7*-*/*-22322*-*/*-22323*-*-
PLUG HSG: *-1971*7*-*/*-22322*-*/*-22323*-*-

3. PRODUCT SPEC: 108-106118

4. APPLICATION SPEC: 114-106118


5. This product has not completed validation testing.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY WU 09JUL2012 CHK HAPYE WU 09JUL2012 APVD YUHONG MAO 09JUL2012		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		NAME DOUBLE LOCK PLATE, DOUBLE ROW POWER TRIPLE LOCK -	
MATERIAL		PRODUCT SPEC 108-106118 APPLICATION SPEC 114-106118 WEIGHT -		SIZE A2	CAGE CODE 00779
		DRAWING NO C-1971778 RESTRICTED TO -		SCALE - SHEET 1 OF 2 REV A3	
		Customer Drawing			


D

D



C

C



B

B

2*6 POSITIONS

2*5 POSITIONS

2*4 POSITIONS

2*3 POSITIONS

2*6	LEVEL 2	2-1971778-6
	LEVEL 1	1971778-6
2*5	LEVEL 2	2-1971778-5
	LEVEL 1	1971778-5
2*4	LEVEL 2	2-1971778-4
	LEVEL 1	1971778-4
2*3	LEVEL 1	1971778-3
	LEVEL 2	2-1971778-3
POS.	MATERIAL	P/N

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.35

2 PLC ± 0.25

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

DWN TOMMY WU 09JUL2012

CHK HAPYE WU 09JUL2012

APVD YUHONG MAO 09JUL2012

PRODUCT SPEC 108-106118

APPLICATION SPEC 114-106118

WEIGHT -

Customer Drawing

TE Connectivity

NAME DOUBLE LOCK PLATE, DOUBLE ROW POWER TRIPLE LOCK

SIZE A2

CAGE CODE 00779

DRAWING NO C-1971778

RESTRICTED TO -

SCALE - SHEET 2 OF 2 REV A3