





In case that the application demands a high level of reliability, such as automotive, please contact a company representative for further information.



RECOMMENDED PC BOARD HOLE PATTERN



PART No.	HRS No.	PIN	A	B	C	D	POLARIZING KEY MOUNT
HIF3FC- 10PA-2.54DSA(71)	CL616-0161-4-71	10	20.2	17.5	10.16	4.1	NONE
HIF3FC- 14PA-2.54DSA(71)	CL616-0162-7-71	14	25.28	22.58	15.24	4.1	1 ON RH SIDE
HIF3FC- 16PA-2.54DSA(71)	CL616-0163-0-71	16	27.82	25.12	17.78	4.1	1 EACH ON LH & RH SIDE.
HIF3FC- 20PA-2.54DSA(71)	CL616-0164-2-71	20	32.9	30.2	22.86	4.1	
HIF3FC- 26PA-2.54DSA(71)	CL616-0165-5-71	26	40.52	37.82	30.48	4.1	
HIF3FC- 30PA-2.54DSA(71)	CL616-0166-8-71	30	45.6	42.9	35.56	4.1	
HIF3FC- 34PA-2.54DSA(71)	CL616-0167-0-71	34	50.88	47.98	40.64	4.1	
HIF3FC- 40PA-2.54DSA(71)	CL616-0168-3-71	40	58.3	55.6	48.26	4.1	
HIF3FC- 50PA-2.54DSA(71)	CL616-0169-6-71	50	71.0	68.3	60.96	4.1	
HIF3FCA-50PA-2.54DSA(71)	CL616-0170-5-71	50	71.0	68.3	60.96	26.96	

- NOTE 1 > *HIF3FC-10PA-2.54DSA(71)* HAS NO STAND-OFF.
2 > THE NUMBER OF POLARIZING KEY MOUNT DIFFERS AS TO THE NUMBER OF PIN, REFER TO THE TABLE.
3 * * INDICATES THE NUMBER OF PIN.
4 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

1	POLYBUTYLENE TEREPHTHALATE	BLACK, UL94 V-0	4	BRASS	CONTACT AREA: GOLD 0.2μ m min. MOUNTING AREA: TIN 2μ m min. UNDER PLATING: NICKEL 2μ m min.
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD) CL			DESIGNED T. NODA	CHECKED H. Doi	APPROVED H. Okawa
SCALE FREE			DRAWN T. NODA		
UNITS mm					
DRAWING NO. EDC3-151845-21					
PART NO. HIF3FC-**PA-2.54DSA(71)					
CODE NO. CL616					

TO	
PCK	