


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HQ	00		FI	REV PER ECO 12-016455	13SEP2012	DW	GG
			G	REVISED PER ECO-18-008420	01JUN2018	CR	JLM

NOTES: UNLESS OTHERWISE SPECIFIED.

1. FABRICATE TO MEET IPC - 6012, CLASS 2.
INSPECT TO MEET IPC - A - 600, CLASS 2.
2. PRIMARY AND SECONDARY SIDES SHOWN
3. MATERIAL: FR-408 PCB.
1/2 OZ. COPPER BOTH SIDES.
DIELECTRIC CONSTANT @ 1MHZ 4.2±0.1.
4. FINISH:
A: 1/2 Oz COPPER PLATING
B: SOLDERMASK OVER BARE COPPER (SMOBC).
C: MASK BOTH SIDES OF PCB WITH LPI SOLDERMASK.
SOLDERMASK COLOR: ORANGE.
D: E.N.I.G PLATING
5. TWO PLACE TOLERANCES: ±0.23
6. PACKAGING: SINGULATED PARTS TO BE SECURELY
SHRINK WRAPPED, BAGGED OR VACUUM PACKED IN BULK.
7. PARTS ARE COMPLIANT TO ROHS STANDARDS PER TYCO
ELECTRONICS STANDARD TEC-138-702.
8. CONSULT TYCO ELECTRONICS DATA SHEET DS1513349
9. CONTACT TYCO ELECTRONICS ENGINEERING
PRIOR TO DESIGNING INTO AN APPLICATION
10. PACKAGING: TAPE & REEL (SEE PAGE 2).



FOR TAPE AND REEL PACKAGING, ORDER P/N 1513349-1
FOR BULK PACKAGING, ORDER P/N 1513349-2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN VG	12JUN2007	Tyco Electronics Rochester, New York 14623	
DIMENSIONS: mm		CHK -	-	NAME Bluetooth 802.11b Antenna	
		APVD -	-	SIZE A300779	
		PRODUCT SPEC -	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC -	-	DRAWING NO C-1513349	
MATERIAL -		WEIGHT -	-	RESTRICTED TO	
FINISH -		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 2
				REV G	

