


Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.



NOTE: ① ACROSS FLATS OF HEXAGON SOCKET OF REF.NO. ⑫, ⑭: 1.27.
② THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑩: 2 N·m.
LOCTITE 271, LOCTITE OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF.NO. ⑩ FROM LOOSENING.
③ THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑫, ⑭: 0.3 TO 0.4 N·m.
④ ROTATION EXAMPLES OF REF.NO. ① AND ⑩ ARE SHOWN.

7	STEEL	ZINC CHROMATED	14	STEEL	NICKEL PLATING M2.6x0.45x3
6	BRASS	NICKEL PLATING	13	BRASS	
5	SIR	(BLACK)	12	STEEL	NICKEL PLATING M2.6x0.45x2
4	BERYLLIUM COPPER	SILVER PLATING 2μm min.	11	NBR	(BLACK)
3	BERYLLIUM COPPER	SILVER PLATING 2μm min.	10	BRASS	NICKEL PLATING
2	PBT	(BLACK) UL94V-0	9	SIR	(BLACK)
1	ZINC ALLOY	NICKEL PLATING	8	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		<i>S. Komatsu</i>	<i>S. Komatsu</i>	<i>E. Kunita</i>	<i>M. Saito</i>	
		06.03.20	06.03.20	06.03.20	06.03.20	
DRAWING NO. EDC3-043812-73		PART NO. HR22-12TPD-20S(73)				
SCALE 2 : 1		CODE NO. CL122-0011-2-73				1/1
UNITS mm		HRS HIROSE ELECTRIC CO., LTD.				

TO
R