



Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.



NOTE: 1 APPLICABLE CRIMPING CONTACT : HR22-SC-222(CL122-0008-8)
(APPLICABLE WIRE : AWG#24~28, OUTER DIMENSION OF JACKET: φ 1.15MAX)
APPLICABLE CONTACT EXTRACTION TOOL : RP6-SC-TP(CL150-0039-0)
2 ACROSS FLATS OF HEXAGON SOCKET OF REF.NO. ⑩, ⑫: 1.27.
3 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑧: 2 N·m.
LOCTITE 271, LOCTITE OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF.NO. ⑧ FROM LOOSENING.
4 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑩, ⑫: 0.3 TO 0.4 N·m.
5 ROTATION EXAMPLES OF REF.NO. ① AND ⑧ ARE SHOWN.

5					6					7					8				
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△					△					△				
△					△					△					△				
△					△					△					△				

6	PHOSPHOR BRONZE	NICKEL PLATING	12	STEEL	NICKEL PLATING M2.6×0.45×3		
5	STEEL	ZINC CHROMATED	11	BRASS			
4	BRASS	NICKEL PLATING	10	STEEL	NICKEL PLATING M2.6×0.45×2		
3	SIR	(BLACK)	9	NBR	(BLACK)		
2	PBT	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING		
1	ZINC ALLOY	NICKEL PLATING	7	SIR	(BLACK)		
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS		
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
			J. Komatsu 06.03.17	J. Komatsu 06.03.17	E. Kunita 06.03.18	M. Sato 06.03.20	
		DRAWING NO. EDC3-043648-73		PART NO. HR22-12TPD-20SC(73)			
SCALE 2 : 1		 HIROSE ELECTRIC CO., LTD.		CODE NO. CL122-0010-0-73			1/1
UNITS mm							

TO
R