


Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.

COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△	1	DIS-C-000490	T.H	E.K	07.01.31	△					..
△					..	△					..
△					..	△					..



- NOTES
- 1 TOTAL LENGTH BECOMES 37.3±1 WHEN 6 IS SCREWED INTO 1 COMPLETELY.
 - 2 APPLICABLE CRIMPING CONTACT:HR30-SC-211
(APPLICABLE WIRE:26-30 AWG WIRE JACKET DIAMETER:φ1 MAX)
APPLICABLE CONTACT WITHDRAWAL:HP30-TP
 - 3 THE RECOMMENDED CLUMP TORQUE OF REF. NO.6 TO BE 0.5N·m.
SPACER FOR ASSEMBLY IS AVAILABLE HR30-8P-T02.
STAND FOR ASSEMBLY IS AVAILABLE HR30-8J-12SC-T01.
 - 4 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

3	PBT	(BLACK)	UL94V-0	6	PPS	(BLACK)	UL94V-0
2	PPS	(BLACK)	UL94V-0	5	SYNTHETIC RUBBER	(BLACK)	
1	PPS	(BLACK)	UL94V-0	4	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	

CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		E.KUNII	E.KUNII		M.SATO	
		'05.10.14	'05.10.14	..	'05.10.17	..

SCALE 5 : 1 UNITS mm	DRAWING NO. EDC3-112267-71	PART NO. HR30-8J-12SC(71)	
	HIROSE ELECTRIC CO., LTD		CODE NO. CL130-2016-1-71

