




	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
▲	2	DIS-C-000490	T.H	E.K	07.01.31	▲					. .
▲					. .	▲					. .
▲					. .	▲					. .



NOTES ① TOTAL LENGTH BECOMES 39.8±1 WHEN ⑦ IS SCREWED INTO ① COMPLETELY.  
2 APPLICABLE CRIMPING CONTACT:HR30-PC-211  
(APPLICABLE WIRE:26-30 AWG WIRE JACKET DIAMETER:φ1 MAX)  
APPLICABLE CRIMP CONTACT EXTRACTION TOOL:HR30-TP  
① ③ THE RECOMMENDED CLUMP TORQUE OF REF. NO. ⑦ TO BE 0.5N · m.  
LOCTITE 271, LOCPRIMER 7649, HENKEL JAPAN IS RECOMMENDED TO PREVENT REF. NO. ⑦ FROM LOOSENING.  
SPACER FOR ASSEMBLY IS AVAILABLE HR30-8P-T02.  
TABLE FOR ASSEMBLY IS AVAILABLE HR30-8P-12PC-T01.  
④ 4 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,  
DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.



4	STAINLESS STEEL						
3	PBT	(BLACK)	UL94V-0	7	PPS	(BLACK)	UL94V-0
2	SIR	(RED)		6	CR	(BLACK)	
1	PPS	(BLACK)	UL94V-0	5	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	
CODE NO.(OLD)			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
			M.HANYU '05. 8. 8	H.NAGANO '05. 8. 8	E.KUNII '05. 8. 10	M.SATO '05. 8. 10	. .
		DRAWING NO.		PART NO.			
SCALE 2 : 1		EDC3-112397-71		HR30-8P-12PC(71)			
UNITS 		HIROSE ELECTRIC CO., LTD		CODE NO.		CL130-0015-8-71	
						1 / 1	