



- NOTES
- 1 PLATING(REF.NO.③)
CONTACT AREA : GOLD 0.2μm min
OTHERS : GOLD AND NICKEL
UNDER PLATING : NICKEL 2μm min
 - 2 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑦ TO BE 1.5 TO 2N·m.
THREAD LOCKER TO THE THREADED PORTION OF REF.NO.① IS RECOMMENDED TO PREVENT REF.NO. ⑦ FROM LOOSING.
 - 3 RECOMMENDED THREAD LOCKER:LOCTITE 263, HENKEL JAPAN LTD.
 - 4 WHEN THIS CONNECTOR IS MOUNTED ON TO PANEL, BE CAREFUL REF.NO. ⑤ IS ASSEMBLED SURELY INTO THE GROOVE OF REF.NO.① AS SHOWN IN THIS FIGURE TO KEEP WATERPROOF EFFECTIVENESS.

4	PHOSPHOR BRONZE	NICKEL PLATING			
3	COPPER ALLOY	1	7	STEEL	NICKEL PLATING
2	PPS	(BLACK) UL94V-0	6	STEEL	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	5	CHLOROPRENE RUBBER	(BLACK)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 4 : 1	COUNT 3	DESCRIPTION OF REVISIONS DIS-C-00001698	DESIGNED HY. KISHI
		APPROVED : MR. YOSHIDA	05. 01. 05	DRAWING NO.	EDC3-114149-00
		CHECKED : MO. SATOH	05. 01. 05	PART NO.	LF07WBR-3S
		DESIGNED : YH. YAMADA	05. 01. 05	CODE NO.	CL136-1004-5-00
		DRAWN : YH. YAMADA	05. 01. 05		
					1/1