







Oct.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.



- NOTES 1. APPLICABLE WIRE IS AWG #16~#18.(UL1007,UL1015)
INSULATION DIAMETER ϕ 3.30mm MAX.
2. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
(CRIMP HEIGHT etc.) WILL BE SPECIFIED ACCORDING TO
AWG # OR WIRE APPLIED.
3. ONE PACKAGE CONSISTS OF 100 PCS.
4. REFER TO ATAI-E3038 FOR CRIMP QUALITY STANDARDS.

				1		COPPER ALLOY		CONTACT AREA : GOLD PLATING 0.2μm MIN. TERMINAL AREA : TIN PLATING 1μm MIN. UNDER PLATING : NICKEL PLATING 0.5μm MIN.		
NO.	MATERIAL		FINISH , REMARKS			NO.	MATERIAL		FINISH , REMARKS	
UNITS mm		SCALE 5 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-E-004910		DESIGNED TY. MIURA		CHECKED NM. NISHIMATSU	DATE 14. 01. 20
 HIROSE ELECTRIC CO., LTD.			APPROVED : RI. TAKAYASU 12. 12. 11			DRAWING NO. EDC3-128191-00				
			CHECKED : AH. KODAMA 12. 12. 11			PART NO. PQ50-1618SCA				
			DESIGNED : TY. MIURA 12. 12. 10			CODE NO. CL236-2044-3-00				
			DRAWN : TY. MIURA 12. 12. 10			 1/1				