

NOTE

1.梱包数量：1000個/リール
NUMBER OF CONNECTORS：1000 PCS/REEL

2.リードテープ長さ LEAD TAPE LENGTH

引き出し方向
PULL OUT DIRECTION

20PCS. MIN. トップテープ接着部（空エンボス）
TOP TAPE BONDED PART. (EMPTY)

部品挿入部
COMPONENT
SUPPLIER

末端部
（空部）
TAIL PART
(EMPTY)
40 MIN.

400 MIN.


3.52610-**15のアクチュエータはハウジング内に押し下げた状態とする。
詳細寸法については図面 526101000 PSD 000 を参照下さい。
ACTUATOR OF PART NO. 52610-**15 SHOULD BE LOCKED.
RE DETAILD DIMENSIONS, SEE 526101000 PSD 000.

4.材料 MATERIAL
キャリアテープ：ポリプロピレン
トップテープ：PET, PE, PEF
リール：ポリスチレン <リサイクル材を含む>
CARRIER TAPE：POLYPROPYLENE
TOP TAPE：PET, PE, PEF
REEL：POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>

5.本製品は52610シリーズの接点金めっき品である。
THIS PRODUCT IS Au-CONTACT OF 52610 SERIES.

6.本製品は乾燥剤入り、ハイバリア梱包仕様である。
THIS PRODUCT ISHIGH BARRIER PACKAGE WITH DESICCANT.



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
RELEASED	EC NO: 106044 DRWN: YMIZUNO02 CHK'D: YKOBAYASHI02 APPR: TKUSUHARA01	2016/10/12 2016/12/28 2016/12/28	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	MODEL NO. 52610-**72				
			ANGULAR TOL ± 3.0 °		MM	---	1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG				
			4 PLACES	± 0.2	DRWN BY	DATE					
			3 PLACES	± 0.2	CHK'D BY	DATE					
			2 PLACES	± 0.2	YKOBAYASHI02	2016/12/28					
			1 PLACE	± 0.2	APPR BY	DATE	PRODUCT CUSTOMER DRAWING				
			0 PLACES	± 0.2	TKUSUHARA01	2016/12/28	SERIES	MATERIAL NUMBER	CUSTOMER		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION	52610	SEE CHART	GENERAL		
					A3		DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER	
							526100000	PSD	000	1 OF 5	






24	29.4	25.4	15.25	11.32	52610-1072	10
			14.25	10.32	52610-0972	9
			13.25	9.32	52610-0872	8
			12.25	8.32	52610-0772	7
			11.25	7.32	52610-0672	6
			10.25	6.32	52610-0572	5
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
RELEASED	EC NO: 106044 DRWN: YMIZUNO02 CHK'D: YKOBAYASHI02 APPR: TKUSUHARA01	2016/10/12 2016/12/28 2016/12/28	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®			
					MM		---					
			ANGULAR TOL ± 3.0 °		DRWN BY		DATE		1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG			
			4 PLACES ± 0.2		YMIZUNO02		2016/10/12					
			3 PLACES ± 0.2		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING			
			2 PLACES ± 0.2		YKOBAYASHI02		2016/12/28					
			1 PLACE ± 0.2		APPR BY		DATE		SERIES 52610			
			0 PLACES ± 0.2		TKUSUHARA01		2016/12/28					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION		CUSTOMER GENERAL			
					A3							
A	REV				DOCUMENT NUMBER 526100000				DOC TYPE PSD	DOC PART 000	SHEET NUMBER 2 OF 5	

RELEASE STATUS		RELEASE DATE	
----------------	--	--------------	--



RELEASE STATUS		RELEASE DATE	
----------------	--	--------------	--





44	49.4	45.4	31.25	27.32	52610-2672	26
			30.25	26.32	52610-2572	25
			29.25	25.32	52610-2472	24
			28.25	24.32	52610-2372	23
			27.25	23.32	52610-2272	22
			26.25	22.32	52610-2172	21
			25.25	21.32	52610-2072	20
			24.25	20.32	52610-1972	19
			23.25	19.32	52610-1872	18
			22.25	18.32	52610-1772	17
			21.25	17.32	52610-1672	16
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED EC NO: 106044 DRWN: YMIZUNO02 CHK'D: YKOBAYASHI02 APPR: TKUSUHARA01	2016/10/12	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE		molex® 1.0 FPC CONN ZIF ASSY SMT ST EMBSTP PKG									
	2016/12/28		MM		---											
	2016/12/28		DRWN BY		DATE											
	REV				ANGULAR TOL ± 3.0 °		YMIZUNO02		2016/10/12		PRODUCT CUSTOMER DRAWING					
				4 PLACES	±	0.2	CHK'D BY		DATE							
				3 PLACES	±	0.2	YKOBAYASHI02		2016/12/28							
				2 PLACES	±	0.2	APPR BY		DATE							
				1 PLACE	±	0.2	TKUSUHARA01		2016/12/28							
				0 PLACES	±	0.2	DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER		CUSTOMER		
	A				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				52610	SEE CHART		GENERAL		
								DOCUMENT NUMBER	526100000		DOC TYPE	PSD	DOC PART	000	SHEET NUMBER	4 OF 5

RELEASE STATUS		RELEASE DATE	
----------------	--	--------------	--



RELEASE STATUS		RELEASE DATE	
----------------	--	--------------	--



参考基盤レイアウト
RECOMMENDED P.C.BOARD
PATTERN LAYOUT (REFERENCE)

マスク厚 : 120μm
マスク開口率 : 100%
SCREEN THICKNESS : 120 MICROMETER
SCREEN OPEN RATIO : 100%

注記(NOTES):

1.材質 MATERIAL

ハウジング：46ナイロン、ガラス充填、UL94V-0、ナチュラル(白色)
 アクチュエータ：PPS、ナチュラル(茶色)、ガラス充填、UL94V-0
 ターミナル：リン青銅(t=0.32)
 HOUSING：46NYLON, GLASS FILLED, UL94V-0, NATURAL(WHITE)
 ACTUATOR：PPS, NATURAL(BROWN), GLASS FILLED, UL94V-0
 TERMINAL：PHOSPHOR BRONZE(t=0.32)

2.めっき仕様 PLATING

ターミナル TERMINAL

接点部：金めっき(0.1μm以上)
テール部：錫めっき(1.0μm以上)
下地：ニッケルめっき(1.0μm以上)
CONTACT : GOLD PLATING (0.1 MICROMETER MINIMUM)
TAIL : MATTE TIN (1.0 MICROMETER MINIMUM)
UNDER PLATE : NICKEL PLATING (1.0 MICROMETER MINIMUM)

△₃ ソルダータール半田付け面のズレ量は、基準面 **F** に対し

上方向0.05MAX.、下方向0.15MAX.とする。

MISALIGNMENT OF SOLDER TAILS FROM [F] UPPER DIREVTION : 0.05 MAX.

LOWER DIRECTION :0.15 MAX.

△ 4 偶数極に適用。


APPLY FOR EVEN CIRCUIT.

5.エンボステーブ梱包時は、アクチュエータがロックした状態とする。


IN THE PACKAGE, ACTUATOR SHOULD BE LOCKED.

6.本製品は52610シリーズの接点金めっき品である。

THIS PRODUCT IS Au-CONTACT OF 52610 SERIES.




適合FPC/FFC推奨寸法
APPLICABLE FPC/FFC
RECOMMENDED DIMENSION
(仕上がり厚さ : 0.3±0.05)
(THICKNESS : 0.3±0.05)



FPC構成推奨仕様

RECOMMENDED STRUCTURE OF FPC



FFC構成推奨仕様

RECOMMENDED STRUCTURE OF FFC

FPC/FFCについて：

抜き方向は、導体側から補強板側を推奨致します。

尚、接着剤の接点部への付着は導通不良の原因になりますので、
染み出しが無い様お願い致します。

ABOUT FPC/FFC:

RECOMMENDED PUNCHER DIRECTION:

FROM CONDUCTOR SIDE TO STIFFNER SIDE





PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND

BECAUSE THERE IS A POSSIBILITY THAT THE EXTRA ADHESIVE


CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED				molex							
		mm		---													
		GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 600129 DRWN: YCHEN128 2018/04/11 CHK'D: KTAKAHASHI 2018/04/12 APPR: NUKITA 2018/04/13				1.0 FPC CONN ZIF S/T HOUSING ASSY							
		ANGULAR TOL ± 3.0°															
GENERAL TOLERANCES (UNLESS SPECIFIED)		4 PLACES		± 0.03		INITIAL REVISION: DRWN: YMIZUNO02 2016/10/12 APPR: TKUSUHARA01 2016/12/28				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
		3 PLACES		± 0.03						526101000		PSD		000		B	
		2 PLACES		± 0.05													
		1 PLACE		± 0.1													
		0 PLACES		± 0.2													
10 UNDER		±0.2		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
10 OVER 30 UNDER		±0.25															
30 OVER		±0.3															
								A3-SIZE		52610		SEE TABLE		GENERAL		2 OF 2	


10 9 8 7 6 5 4 3 2 1



REVISED EC NO.: J2012-0856 DRWN: KMIYAHARA 2012/01/05 CHKD: KMIYAHARA 2012/01/05 APPR: KMORI KAWA 2012/02/07	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY M. NABEI	DATE '05/07/21	TITLE 1.0 FPC CONN ZIF FOR SMT ST -LEAD FREE-			
		10 OVER 30 UNDER	± 0.25	CHECKED BY K. TOYODA	DATE '05/07/21				
		30 OVER	± 0.3	APPROVED BY N. UKITA	DATE '05/07/21	 MOLEX INCORPORATED			
		ANGULAR ±3 °		MATERIAL NO.					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52610-036		1 OF 2		
	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



適合FPC推奨寸法
APPLICABLE FPC RECOMMENDED DIM.
仕上がり厚さ(THICKNESS): 0.3±0.05



注記(NOTES):

1. 材料(MATERIAL)

ハウジング(HOUSING): 46NYLON , UL94V-0
アクチュエータ(ACTUATOR): PPS , UL94V-0
ターミナル(TERMIAL): リン青銅 (t 0.32)

PHOS-BRO

接点部: 金メッキ 0.1μm 以上

テール部: 錫メッキ 1μm 以上

下地: ニッケルメッキ 1μm 以上

CONTACT: GOLD 0.1 MICROMETER MINIMUM

TAIL: MATTE TIN 1 MICROMETER MINIMUM

NICKEL: UNDER 1 MICROMETER MINIMUM

2. エンボステープ梱包時は、アクチュエータがロックした状態とする。
IN THE PACKAGE , ACTUATOR OF PART NO. 52610-**59 SHOULD BE LOCKED.

3. ソルダータール半田付け面のズレ量は、基準面 F に対し上方向 0.05 MAX.
下方向 0.15 MAX. とする。
MISALIGNMENT OF SOLDER TAILS FROM F UPPER DIRECTION : 0.05 MAX. ,
LOWER DIRECTION : 0.15 MAX.


4. 偶数極に適用。
APPLY FOR EVEN CIRCUIT.

5. 本製品は 52610 シリーズの接点金メッキ品である。
THIS PRODUCT IS Au-CONTACT OF 52610 SERIES.

36.6	34.85	31.2	29	52610-3072	52610-3015	30
32.6	30.85	27.2	25	52610-2672	52610-2615	26
31.6	29.85	26.2	24	52610-2572	52610-2515	25
30.6	28.85	25.2	23	52610-2472	52610-2415	24
28.6	26.85	23.2	21	52610-2272	52610-2215	22
26.6	24.85	21.2	19	52610-2072	52610-2015	20
25.6	23.85	20.2	18	52610-1972	52610-1915	19
24.6	22.85	19.2	17	52610-1872	52610-1815	18
23.6	21.85	18.2	16	52610-1772	52610-1715	17
22.6	20.85	17.2	15	52610-1672	52610-1615	16
21.6	19.85	16.2	14	52610-1572	52610-1515	15
20.6	18.85	15.2	13	52610-1472	52610-1415	14
19.6	17.85	14.2	12	52610-1372	52610-1315	13
18.6	16.85	13.2	11	52610-1272	52610-1215	12
17.6	15.85	12.2	10	52610-1172	52610-1115	11
16.6	14.85	11.2	9	52610-1072	52610-1015	10
15.6	13.85	10.2	8	52610-0972	52610-0915	9
14.6	12.85	9.2	7	52610-0872	52610-0815	8
12.6	10.85	7.2	5	52610-0672	52610-0615	6
11.6	9.85	6.2	4	52610-0572	52610-0515	5

52610-**15	D	(C)	B	(A)	EMBOSSD TAPE	MATERIAL. NO.	極数 CKT.
MODEL NO.					ORDER No. オーダー番号		

REVISED EC NO. J2012-0856 DRWNG:KMIYAHARA 2012/01/05 CHKD:KMIYAHARA 2012/01/05 APPR:KMORIKAWA 2012/02/07	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY M.NABEI	DATE '05/07/21	TITLE 1.0 FPC CONN ZIF FOR SMT ST -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY K.TOYODA	DATE '05/07/21					
		30 OVER	± 0.3	APPROVED BY N.UKITA	DATE '05/07/21	MOLEX INCORPORATED				
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.				SHEET NO.
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52610-036				2 OF 2	
	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



NOTES

- 梱包数量：1000個/リール
NUMBER OF CONNECTORS : 1000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH
20PCS. MIN. トップテープ接着部 (空エンボス)
TOP TAPE BONDED PART. (EMPTY)
部品挿入部
COMPONENT
SUPPLIER
末端部
(空部)
TAIL PART
(EMPTY)
400 MIN.
40 MIN.
- 52610-**15 のアクチュエータはハウジング内に押し下げた状態とする。
詳細寸法については図面 SD-52610-036 を参照下さい。
ACTUATOR OF PART NO. 52610-**15 SHOULD BE LOCKED.
RE DETAILED DIMENSIONS , SEE SD-52610-036.
- 材料 (MATERIAL)
キャリアテープ (CARRIER TAPE) : ポリプロピレン (POLYPROPYLENE)
トップテープ (TOPTAPE) : PET , PE , PEF
リール (REEL) : ポリスチレン (P S) <リサイクル材を含む>
POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>
- 本製品は 52610 シリーズの接点金メッキ品である。
THIS PRODUCT IS Au-CONTACT OF 52610 SERIES.
- 本製品は乾燥剤入り、ハイバリア梱包仕様である。
THIS PRODUCT IS HIGH BARRIER PACKAGE WITH DESICCANT.

REVISED EC NO: J2012-0856 DRWN: KMIYAHARA 2012/01/05 CHKD: KTAHASHI 2012/01/05 APPR: KMORIKAWA 2012/02/07		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	52610-**72	MODEL NO.
		10 UNDER ±0.2		DRAWN BY M. NABEI		DATE '05/07/21	DESIGN UNITS METRIC	
		10 OVER 30 UNDER ±0.25		CHECKED BY K. TOYODA		DATE '05/07/21	1.0 FPC CONN SMT ZIF EMBSTP PKG -LEAD FREE- MOLEX INCORPORATED	
		30 OVER ±0.3		APPROVED BY N. UKITA		DATE '05/07/21		
REV	DESCRIPTION	ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52610-037		1 OF 5
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F




E

D

C

B


A



52610-**-72
MODEL NO.

24	29.4	25.4	15.25	11.32	52610-1072	10
			14.25	10.32	52610-0972	9
			13.25	9.32	52610-0872	8
			11.25	7.32	52610-0672	6
			10.25	6.32	52610-0572	5
キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL. NO.	極数 CKT.

REVISED EC NO: J2012-0856 DRWN:KMIYAHARA 2012/01/05 CHKD:KTAKAHASHI 2012/01/05 APPR:KMORIKAWA 2012/02/07	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY M. NABEI	DATE '05/07/21	TITLE 1.0 FPC CONN SMT ZIF EMBSTP PKG -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY K. TOYODA	DATE '05/07/21					
		30 OVER	± 0.3	APPROVED BY N. UKITA	DATE '05/07/21	MOLEX INCORPORATED				
		ANGULAR ±3 °		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52610-037			2 OF 5	
	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								



						32		37.4		33.4		20.25		16.32		52610-1572		15					
												19.25		15.32		52610-1472		14					
												18.25		14.32		52610-1372		13					
												17.25		13.32		52610-1272		12					
												16.25		12.32		52610-1172		11					
52610-**72						キャリアテープ幅 CARRIER TAPE WIDTH		D		C		(B)		(A)		MATERIAL. NO.		極数 CKT.					
MODEL NO.																							
GENERAL TOLERANCES (UNLESS SPECIFIED)						DIMENSION STYLE MM ONLY				SCALE ---		DESIGN UNITS METRIC		◎ □ THIRD ANGLE PROJECTION									
						10 UNDER		± 0.2		DRAWN BY M. NABEI		DATE '05/07/21		TITLE 1.0 FPC CONN SMT ZIF EMBSTP PKG -LEAD FREE- MOLEX INCORPORATED									
						10 OVER 30 UNDER		± 0.25		CHECKED BY K. TOYODA		DATE '05/07/21											
						30 OVER		± 0.3		APPROVED BY N. UKITA		DATE '05/07/21											
						ANGULAR		± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO. 3 OF 5									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SEE TABLE				SD-52610-037													
						SIZE A3				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F


E

D

C

B

A



52610-**-72
MODEL NO.

44	49.4	45.4	31.25	27.32	52610-2672	26		
			30.25	26.32	52610-2572	25		
			29.25	25.32	52610-2472	24		
			27.25	23.32	52610-2272	22		
			25.25	21.32	52610-2072	20		
			24.25	20.32	52610-1972	19		
			23.25	19.32	52610-1872	18		
			22.25	18.32	52610-1772	17		
			21.25	17.32	52610-1672	16		
キャリアテープ幅 CARRIER TAPE WIDTH			D	C	(B)	(A)	MATERIAL. NO.	極数 CKT.

REVISED EC NO. J2012-0856 DRAWN:KMIYAHARA 2012/01/05 CHKD: APPR:KMORI KAWA 2012/02/07	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY M.NABEI	DATE '05/07/21	TITLE 1.0 FPC CONN SMT ZIF EMBOSTP PKG -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY K.TOYODA	DATE '05/07/21					
		30 OVER	± 0.3	APPROVED BY N.UKITA	DATE '05/07/21	MOLEX INCORPORATED				
		ANGULAR	± 3 °	MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-52610-037		4 OF 5		
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
	REV									

