






CONTACT ORIENTATION ON ROLL


NOTES : (UNLESS OTHERWISE SPECIFIED)

- MATERIAL :
 - CONTACT BODY : COPPER ALLOY.
 - OUTER SPRING : STAINLESS STEEL.
- SPECIFICATIONS :
 - CURRENT RATING : 5A MAX.
 - TERMINATION TYPE : CRIMPING.
 - WIRE RANGE : 26~24AWG.
 - WIRE INSULATION DIA(MAX) : $\varnothing$ 2.6mm.
- ROHS COMPLIANT.
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- AVAILABLE TOOLS :
 - HAND CRIMPER : MFX-3954.
 - CRIMP APPLICATOR : MFX-3957.
 - EXTRACTION TOOL : QXRT20.

P/N	CONTACT PLATING(MATING AREA)
SS24W2T	TIN PLATING OVER NICKEL.
SS24W2F	GOLD FLASH PLATING OVER NICKEL.
SS24W2G10	10 μ "GOLD PLATING OVER NICKEL.
SS24W2G15	15 μ "GOLD PLATING OVER NICKEL.
SS24W2G30	30 μ "GOLD PLATING OVER NICKEL.



SECTION A-A



SECTION B-B

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	NOV-9-17	ROOKEI	TOMMY

TITLE: ECO-MATE, SOCKET CONTACT, STAMPED, 24-26AWG, SIZE 20

DWG NO:

SS24W2XX

REV: A1

SH: 1

OF: 1

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC $\pm$0.30 2 PL DEC $\pm$0.15 3 PL DEC $\pm$0.08 Fractions $\pm$1/64 Angles $\pm$1° 3) Note reference = 		SIGNATURES DATE DRAWN: ROOKIE NOV-9-17 CHECKED: ORION NOV-9-17 ENGINEER: APPROVAL: TOMMY NOV-9-17 CUSTOMER: THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 ECO-MATE, SOCKET CONTACT, STAMPED, 24-26AWG, SIZE 20
MATERIAL SPECIFICATIONS:		SIZE TYPE DWG NO: B C- SS24W2XX REVISION A1	
PROCESS SPECIFICATIONS:			
NEXT ASSY:		SCALE: NONE	SHEET 1 OF 1