






REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	RELEASED DRAWING	Nov-9-17	Rookie Tommy
A2	-	ADD THE GS PART NUMBER	Jan-28-19	Blink Tommy



- CONTACT ORIENTATION ON ROLL**
- NOTES : (UNLESS OTHERWISE SPECIFIED)
- MATERIAL :
 - CONTACT BODY : COPPER ALLOY.
 - OUTER SPRING : STAINLESS STEEL.
 - SPECIFICATIONS :
 - CURRENT RATING : 5A MAX.
 - TERMINATION TYPE : CRIMPING.
 - WIRE RANGE : 30~28AWG.
 - WIRE INSULATION DIA(MAX) : ϕ 1.8mm.
 - ROHS COMPLIANT.
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
 - AVAILABLE TOOLS :
 - HAND CRIMPER : MFX-3954.
 - CRIMP APPLICATOR : MFX-3957.
 - EXTRACTION TOOL : QXRT20.

P/N	CONTACT PLATING(MATING AREA)
SS28W2T	TIN PLATING OVER NICKEL.
SS28W2N	NICKEL PLATING OVER COPPERIZE.
SS28W2F	GOLD FLASH PLATING OVER NICKEL.
SS28W2G5	5 μ "GOLD PLATING OVER NICKEL.
SS28W2G10	10 μ "GOLD PLATING OVER NICKEL.
SS28W2G15	15 μ "GOLD PLATING OVER NICKEL.
SS28W2G30	30 μ "GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED		SIGNATURES	
1) All dimensions are in metric(mm).		DRAWN	DATE
2) Tolerances are as follows:		Blk	Jan-28-19
3 PL DEC 20-18		CHECKED	Idl
3 PL DEC 20-18		ENGINEER	Jan-28-19
3) Note reference =		APPROVAL	Tommy
MATERIAL SPECIFICATIONS:		CUSTOMER	Jan-28-19
PROCESS SPECIFICATIONS:		ECO-MATE, SOCKET CONTACT, STAMPED, 28-30AWG, SIZE 20	
NEXT ASSY:		SIZE	TYPE
		B	C-
		SCALE	NONE
		SHEET	1 OF 1

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036