


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	28JUN2015	DW	CW
	A1	ECR-17-002571	23FEB2017	BS	CW
	A2	ECR-17-009384	25DEC2017	RL	CW

ASSEMBLY STATE OF THE PRODUCT, FOR REFERENCE

产品装配状态，供参考




- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 50V
RATED CURRENT: 10A
RATED IMPULSE VOLTAGE: 0.8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CABLE DIAMETER: 3 - 9.5 mm
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No.REFER TO DRAWING:T20200X20XX000)


- 注释:
1. 技术参数:
绝缘材料: PC
额定电压: 50V
额定电流: 10A
额定脉冲电压: 0.8KV
污染等级: 3
阻燃等级: UL94V-0
接线范围: 0.14-2.5 mm² (26-14 AWG)
电缆外径: 3-9.5 mm
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面:T20200X20XX000)

FOR Ø6-9.5mm CABLE
用于直径Ø6-9.5mm 电缆线

FOR Ø3-6mm CABLE
用于直径Ø3-6mm 电缆线



T2580032154-000	PIN-Q2-F	QUINTAX FEMALE CONTACT 4-POS QUINTAX 4-POS母针
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28JUN2015 David Wang	 TE Connectivity		
		CHK 28JUN2015 Chris Wang			
		APVD 28JUN2015 Xiang Xu			
		PRODUCT SPEC 108-137067			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME QUINTAX FEMALE CONTACT 4-POS PIN-Q2-F		
		0 PLC ±-	SIZE A3		
		1 PLC ±-			
		2 PLC ±-			
		3 PLC ±-			
MATERIAL		FINISH	CAGE CODE 00779		
			DRAWING NO T2580032154000		
			RESTRICTED TO		
			Customer Drawing		
			SCALE 2:1		
			SHEET 1 OF 1		
			REV A2		