







- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [0.220±0.003] CENTERS
- 2 SLOT ACCEPTS A 0.54-0.64mm [#23.5-#22] AWG COPPER MAGNET WIRE.
- 3 MATES WITH STANDARD MAG-MATE STYLED POKE-IN TAB TERMINAL.
- 4 WHEN FREE STATE IS COMPRESSED TO 3.23 [0.127] DIMENSION GAP BETWEEN SPRING AND CARRIER IS TO BE 0.30 [0.012] MAX.
- 5 0.0010 [0.000040] MIN TIN OVER 0.00127 [0.000050] MIN NICKEL UNDERPLATE.
- 6 ANTI-FRETTING LUBRICANT APPLIED.
- 7 0.00382 [0.000150] MIN SILVER PLATE OVER 0.00127 [0.000050] MIN NICKEL UNDERPLATE.
- 8 PRELIMINARY - NOT FOR PRODUCTION.

7	4M BRASS	8	1217689-4
5	H04 PHOSPHOR BRONZE	8	1217689-3
5	4M BRASS	8	1217689-2
5	4M BRASS		1217689-1
FINISH		MATERIAL	
		PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SAMUEL D. WYNN CHK MICHAEL S. FEHER APVD KURT A. RANDOLPH		 TE Connectivity			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME		SPECIAL LEAF CONTACT, 300 SERIES MAG-MATE™ —	
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.25[.010] 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC 108-2012 APPLICATION SPEC 114-2046		RESTRICTED TO —	
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —		SIZE A2	
						CAGE CODE 00779	
						DRAWING NO C=1217689	
						SCALE 10:1	
						SHEET 1 of 1	
						REV B1	