


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	A	ACTIVE RELEASE PER ECO-14-001075	140221	GS AT
		B	REVISED PER ECO-15-018025	151215	SS BP
		C	REVISED PER ECO-18-018279	181109	PF AR




PART NUMBER ***-	SUPERCEDED NUMBER	SIZE	(COLOR CODE)	MILITARY PART NUMBER	$\varnothing(A)$ MAX.	$\varnothing(B)$ MAX.	$(C)$ MAX
MS27488-22-2	-	22	BLACK	MS27488-22-2	.066	.045	.500
MS27488-20-2	-	20	RED	MS27488-20-2	.090	.058	.805
MS27488-16-2	-	16	GREEN	MS27488-16-2	.130	.079	.872
MS27488-12-2	-	12	ORANGE	MS27488-12-2	.170	.125	.841
MS27488-16-3	0613-1-1601	16	BLUE	MS27488-16-3	.130	.079	1.472
MS27488-12-3	0613-1-1201	12	YELLOW	MS27488-12-3	.170	.125	1.441

©

DESCRIPTION:  
 SIZE 22, 20, 16  
 AND 12 PER MS27488

3. MATERIAL: PLASTIC ROD, MOLDED AND EXTRUDED-TEMPERATURE LIMIT 200°C MINIMUM. POLYPHENYLSULFONE (PPSU) PER ASTM-D6394. (B)
  2. (INSULATION RESISTANCE SHALL BE 100 MEGAOHMS MINIMUM WHEN TESTED IN ACCORDANCE WITH ASTM D257.)
  1. DIMENSIONS AND TOLERANCES SHOWN FOR REFERENCE ONLY.
- NOTES: UNLESS OTHERWISE SPECIFIED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.S. 130918	 TE Connectivity	
DIMENSIONS: INCHES		CHK A. TEUNISSEN 140122		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. RENGIFO 140221	NAME SEAL, PLUG PER MS27488 ENVELOPE	
0 PLC ±- 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.005 4 PLC ±0.0001 ANGLES ±0.5		PRODUCT SPEC MS27488	SIZE A3	
MATERIAL SEE NOTE 3		APPLICATION SPEC -	CAGE CODE 11139	DRAWING NO MS27488-x-x-x
FINISH -		WEIGHT -	RESTRICTED TO -	
		Customer Drawing	SCALE 15.000	SHEET 1 OF 1 REV C