




13	12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	----	---	---	---	---	---	---	---	---	---


MATERIAL NUMBER	FINISH
43178-4001	999
43178-4002	H901





SECTION W-W
SCALE 10:1
CONDUCTOR CRIMP



SECTION V-V
SCALE 10:1
INSULATION CRIMP



CARRIER STRIP PROGRESSION
SCALE 2:1





- NOTES
- MATERIAL: BRASS
 - FINISH:
999 - UNPLATED
H901 - 20 MICROINCH / 0.5 MICROMETERE MIN. PREPLATED HOT TIN DIP
 - PRODUCT SPECIFICATION: PS-44441-001
 - PACKAGING: TERMINALS ARE WOUND ON 30" REELS WITH PAPER INTERLEAF. 6000 PER REEL.
 - TERMINAL ACCEPTS SINGLE #18 OR #20 AWG STRANDED WIRE, INSULATION: UL TYPE 1015, .098-.110 / 2.50-2.85 DIAMETER, (.031 / 0.79 NOMINAL JACKET WALL THICKNESS) OR DOUBLE 22 AWG.
 - TERMINAL FOR USE IN "SABRE" PLUG HOUSINGS, SERIES 43680. MATES TO 43374 / 43375 SERIES TERMINALS.
 - TERMINAL HAS TPA (TOTAL POSITIONING ASSURANCE) OPTIONAL ACTIVATION FEATURE THAT WHEN ACTIVATED AND USED WITH MOLEX "SABRE" SERIES PLUG HOUSINGS PROVIDES A SECONDARY LOCK SYSTEM WHICH ENSURES AGAINST TERMINAL BACKOUTS.


ADD 2x22 AWG EC NO: UCP2015-5072 DRWN: JMONT 2015/06/01 CHKD: BANDERSON 2015/06/02 APPR: FSMITH 2015/06/15	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 8:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY CSTEWART	DATE 02-23-06	TITLE TERMINAL, MALE CRIMP, 18-20 AWG, .125 WIDE TAB SABRE SERIES, W/ TPA molex				
						CHECKED BY BWIRKUS	DATE 02-23-06					
						APPROVED BY BWIRKUS	DATE 02-23-06					
						MATERIAL NO.	DOCUMENT NO.					
						ANGULAR ±1/2°				SHEET NO.		
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART SD-43178-002 1 OF 1				
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

13	12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	----	---	---	---	---	---	---	---	---	---


MATERIAL NUMBER	FINISH
43178-4001	999
43178-4002	H901





SECTION W-W
SCALE 10:1
CONDUCTOR CRIMP



SECTION V-V
SCALE 10:1
INSULATION CRIMP



CARRIER STRIP PROGRESSION
SCALE 2:1



- NOTES
- MATERIAL: BRASS
 - FINISH:
999 - UNPLATED
H901 - 20 MICROINCH / 0.5 MICROMETERE MIN. PREPLATED HOT TIN DIP
 - PRODUCT SPECIFICATION: PS-44441-001
 - PACKAGING: TERMINALS ARE WOUND ON 30" REELS WITH PAPER INTERLEAF. 6000 PER REEL.
 - TERMINAL ACCEPTS SINGLE #18 OR #20 AWG STRANDED WIRE, INSULATION: UL TYPE 1015, .098-.110 / 2.50-2.85 DIAMETER, (.031 / 0.79 NOMINAL JACKET WALL THICKNESS) OR DOUBLE 22 AWG.
 - TERMINAL FOR USE IN "SABRE" PLUG HOUSINGS, SERIES 43680. MATES TO 43374 / 43375 SERIES TERMINALS.
 - TERMINAL HAS TPA (TOTAL POSITIONING ASSURANCE) OPTIONAL ACTIVATION FEATURE THAT WHEN ACTIVATED AND USED WITH MOLEX "SABRE" SERIES PLUG HOUSINGS PROVIDES A SECONDARY LOCK SYSTEM WHICH ENSURES AGAINST TERMINAL BACKOUTS.

ADD 2x22 AWG EC NO: UCP2015-5072 DRWN: JMONT 2015/06/01 CHKD: BANDERSON 2015/06/02 APPR: FSMITH 2015/06/15	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 8:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION TERMINAL, MALE CRIMP, 18-20 AWG, .125 WIDE TAB SABRE SERIES, W/ TPA molex DOCUMENT NO. SD-43178-002 SHEET NO. 1 OF 1
					DRAWN BY CSTEWART	DATE 02-23-06	TITLE		
					CHECKED BY BWIRKUS	DATE 02-23-06			
					APPROVED BY BWIRKUS	DATE 02-23-06			
					MATERIAL NO.		DOCUMENT NO.		
					SEE CHART				
					SIZE C				
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

ANGULAR ±1/2°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX.
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION