
A1

ECN\* APP'D./DATE 10887 TAM 10/6/94 0 SAFETY ORGANIZATION(S): ECO-09-026495 AEG 11DEC09 THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED RELIABILITY SPECIFICATIONS. IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS STORAGE TEMPERATURE. -40°C TO +85°C STORAGE TEMPERATURE: HAVE BEEN MET: 21 DAYS # 40°C 95% RH HUMIDITY: CURRENT OVERLOAD TEST: TEST SPECIFICATIONS: 6 TIMES RATED CURRENT UL RECOGNIZED UL 1283 FOR 8 SECONDS CSA CERTIFIED CSA 22.2, NO.0, 0.4, 8 INDUCTANCE: VDE APPROVED VDE 565-3, 625 CAPACITANCE: (MEASURED # 1 KHz, 0.25 VAC MAX., 25°C ±1°C) .005µF ±20% 5 AMP., 120 VAC 4 AMP., 250 VAC OPERATING SPECIFICATIONS: LINE TO LINE: .01µF ±20% LINE VOLTAGE/CURRENT: DISCHARGE RESISTOR: 1.5 Mp 4 AMP./40°C, 250 VAC LINE/GROUND AND LINE/LINE 6000 Mm (MIN) AT 100 VDC LINE FREQUENCY: 50-60Hz INSULATION RESISTANCE 20°C AND 50% RH MAX. LEAKAGE CURRENT, EACH (W/O DISCHARGE RESISTOR) .25mA @ 120V 60Hz .42mA @ 250V 50Hz RECOMMENDED RECEIVING INSPECTION HIPOT: LINE TO GROUND -10°C TO +40°C @ RATED CURRENT, I LINES TO GROUND: 1500 VAC FOR 1 MINUTE OPERATING AMBIENT TEMP. RANGE: 1450 VDC FOR 1 MINUTE LINE TO LINE: IN AN AMBIENT, Ta, HIGHER THAN 40°C, THE MAXIMUM OPERATING FILTER APPROVAL: CURRENT, L, IS AS FOLLOWS: THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



This document is proprietary to CORCOM INC. and is not to be reproduced nor used for manufacturing purposes except on CORCOM'S prior written consent. DATE: 4-18-94 APPRVD. 5EFM1SC SEFM150.00