

111

4

3


2

1 LOC CM DIST 53

DRAWING MADE IN THIRD ANGLE PROJECTION

© COPYRIGHT 1975 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓		K	REVISED PER ECR-12-013323	10AUG12
					APPROVED TM



- ① PLATED WITH .000030 GOLD, OVER .000050 NICKEL UNDERPLATE.
- ② GOLD OVER NICKEL ON ENTIRE STAMPING; .000030 GOLD MINIMUM AT POINT OF MEASUREMENT IN CONTACT AREA, GOLD FLASH MINIMUM IN WIRE BARREL.
- ③ INSULATION RANGE: .130 - .200 DIA

.012 BRASS	GOLD	①	350707-7
.012 BRASS	GOLD	②	350707-2
	PRE-TIN		350707-1
MATERIAL	FINISH	PART NO	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.015 ANGLES ±	CONTRACT NO	TE Connectivity		
	DR	M. FEHER 4-13-81		
	CHK	J. S. Heide 6/9/81		
	APPD	R. P. P. 6-10-81		
	APPD			
WIRE RANGE	DSGN APPD	NAME	SPLIT PIN, (LOOSE PIECE)	
20-14 AWG		UNIVERSAL MATE-N-LOK		
INSULATION RANGE	OTHER APPD	SIZE	CODE IDENT NO	DRAWING NO
③		B	00779	350707
		SCALE 4-1	SHEET	

CUSTOMER DRAWING