

183.74

[7.23]

166.60

[6.56]

TOP PANEL - BOTTOM VIEW

190.50

[7.50]

14.29

[.56]

172.64

[6.80]

163.09

[6.42]

Ø4.80 4X

242.57


[9.55]

Ø2.79 8X


[.11]


233.38 [9.19]

[.19]









[inches]

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory mjm@hammondmfg.com for quotes
Solid models of this enclosure available in STEP or IGES.
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes case, cover, 4 cover screws, and 4 rubber feet. Case made from 12 Gauge aluminum (.081"), Top made from 14 Gauge aluminum (.064").

Recommended screw torque 150-175 cN-m (13.3-15.5 lbf-in)

1456	
1456KG4 Regular Enclosure	
Beige Top / Blue Case	1456KG4WHBU
Black Top / Blue Case	1456KG4BKBU
Black Top / Black Case	1456KG4BKBK
ACCESSORIES	
Natural Finish Cover Screws (Pkg 6)	1421J6
[6-32 x 1/4" Self-Tapping Screws]	
Black Cover Screws (Pkg 6)	1421J6BK
[6-32 x 1/4" Self-Tapping Screws]	
Rubber Feet [0.5 x 0.5" Self-adhesive] (Pkg 24)	1421T3

