




REVISION	DATE	REV.
NEW	2017/05/22	A/0



PIN OUT:



NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 500V 500MΩ;
 - Contact resistance: 50 ohm Max;
- RoHS & REACH Compliant.
- PRINT WORD: RW System Cable UTP CAT5E 4 Pairs 26AWG Stranded ISO 11801 100MHZ

MATERIAL LIST:

③	OUTER MOLD	PVC 75A/BLACK	2		DRAWING		PART NAME	CAT. 5E UTP 8P8C TO 8P8C	
②	CONN	RJ45 8P8C PIN GOLD-PLATED TRANSPARENT	2		CUSTOMER		ICON	TOLERANCE	
					CUSTOMER'S ITEM			X. ±1.00	X.X ±0.50
①	CAT. 5E CABLE	UTP CAT. 5E 26AWG (7/0.16) BC*4P PVC JACKET/BLACK OD: 5.2 ± 0.2mm	1		APPRO BY	CHECK BY	DRAWN BY	SCALE	MM
NO.	PARTS. NAME	SPECIFICATION STANDARD	QT'Y	REMARK				PAGE	1/1