

REV	DATE	ECN NUMBER	ECN COMMENT					
007	02 Jul 2018	C03849	11.5 DIMENSION INCORRECT					
006	21 Mar 2018	C03849	NEW BORDER ADDED					


A TURNED BRASS SINGLE NUT FIXING PANEL SOCKET AVAILABLE IN NICKEL OR GOLD PLATED FINISH.  
A CHOICE OF RED OR BLACK INSULATOR IS USEFUL FOR IDENTIFICATION PURPOSES.  
SINGLE NUT FIXING MAKES THESE ADAPTABLE SOCKETS. SUITABLE FOR STACKING ADJACENT TO ONE ANOTHER..

MATERIAL:  
HOUSING  
SOCKET BRASS, BS2874 CZ 131  
SILVER PLATED  
INSULATION  
NUT ACETAL  
BRASS, BS2874 CZ 131  
GOLD FLASH 0.05 MICRONS  
OR NICKEL PLATE  
SOLDER TAG BRASS, BS2874 CZ 131  
GOLD FLASH 0.05 MICRONS  
OR SILVER PLATE  
WASHER BRASS, BS2874 CZ 131  
GOLD FLASH (0.05m)  
OR NICKEL PLATE  
COLOURED WASHER NORYL, BLACK OR RED

RATING:  
RATED CURRENT: 5A.  
RATED VOLTAGE: 50V.  
INSULATION RESISTANCE 100MΩ AT 500 V- DC

FITTING:  
PANEL THICKNESS 3mm MAXIMUM  
MOUNTING HOLE 7.2 Ø mm

### DIMENSIONS



PART NUMBER	COLOUR	PLATING
431-0100	BLACK	NICKEL
431-0500	RED	NICKEL
432-0100	BLACK	GOLD
432-0500	RED	GOLD