




This is issued in strict confidence on condition that it is not used as a basis for manufacture or sale, and that it is not copied,



A ± 0,38 (.015)	B ± 0,13 (.005)	C ± 0,13 (.005)	D ± 0,13 (.005)	E ± 0,38 (.015)	L ± 0,25 (.010)	W ± 0,41 (.016)	K ± 0,25 (.010)
66,93 (2.635)	52,81 (2.079)	61,11 (2.406)	11,07 (.436)	15,37 (.605)	0,99 (.039)	6,84 (.269)	1,52 (.060)

Selected hardware option
with 3,05 (.120) mounting hole

Signal contacts
not shown for clarity




PCB mounting hole Ø (2)	PCB Signal cont Ø (32)
3,05 (.120) ± 0,05 (.002)	1,40 (.055)

NOTE: DO NOT MAKE ASSUMPTIONS REGARDING HOLE LOCATIONS, CHECK EACH DIMENSION

Right angle signal contacts

Mounting hardware
not shown for clarity



Signal contact diameter	Signal contact length from bottom of bracket
Y ± 0,04 (.002)	X ± 0,69 (.027)
1,00 (.040)	4,01 (.158)

DESCRIPTION	MATERIAL	FINISH
Insulator	Polyester	None, (Color Black)
Shells	Steel	Yellow Chromate over Zinc
Signal Contacts	Copper alloy	50 microinches Gold over Nickel
Bracket	Thermo-plastic	None
Unless otherwise specified, dimensions are in mm & (in.) Tolerances are (.XXX = mm) Decimals Angles .X ± 0,20 (.008) X° ± 1.0° .XX ± 0,10 (.004) .XXX ± 0,05 (.002)	Issue Date: 11-Feb-19	Cannon ITT Industries
	CONNECTOR, PLUG, ELECTRICAL COMBO D 36W4 RIGHT ANGLE PCB	
	PART NO.	DDMM36W4PG