




Bild 1. (0.5 - 0.75) mm²




Bild 2. (0.35 - 0.5) mm²
fehlende Masse S. Bild 1.
Missing dimensions see view 1.




Bild 3. Blindstopfen/ Blind Plug
fehlende Masse S. Bild 1.
Missing dimensions see view 1.




Bild 4. (1.0 - 1.5) mm²
fehlende Masse S. Bild 1.
Missing dimensions see view 1.

Bemerkungen / Notes

1	Schraege alternativ zur eckigen Ausfuehrung zulaessig <i>Chamferred alternative to angular design permissible</i>
2	Mittlere Dichtlippe wahlweise gedreht <i>Center sealing lip optionally turned</i>
3	Material: Silikonkautschuk - 50±5 Shore A; selbstschmierend 0elanteil 2±1% Reissdehnung> 375%; ozonbestaendig; warmluftbestaendig 180° <i>Silicon rubber - 50±5 shore A; self-lubricated 2±1% Elongation at break >375%; ozone resistance; warm air resistance 180° C;</i>
4	Used on 8 000 04 11/31/14/34 6 010 01 11/31/14/34 8 000 08 11/31/41/14/34 6 010 07 11/31/41/14/34 6 000 12 14/34 6 010 13 14/34 6 000 15 14/34 6 010 07 41 6 000 06 41
5	Fuer bestehende Anwendungen kann die Einzeldichtung 6 099 39 28 noch fuer einen Isolationsdurchmesser 1.4-1.9 eingesetzt werden. Fuer Neuanwendungen ist der Isolationsbereich auf 1.6-1.9 begrenzt. <i>It's allowable to take the SWS-part 6 099 39 28 also for insulation diameter 1.4-1.9 for existing projects. It's not allowable for new projects</i>

6 099 39 34	C	15460621	01	1.9-2.4	gelb <i>yellow</i>	2 ± 1%
6 099 39 28	C	15441380	01	1.6-1.9 5	grau <i>grey</i>	2 ± 1%
6 099 39 13	C	15441379	01	1.2-1.6	rot <i>red</i>	2 ± 1%
6 099 39 06	C	15441383	01	Blindstopfen <i>Blind plug</i>	weiss <i>white</i>	2 ± 1%
Teile Nr. <i>Part no.</i>	Rev.	Teile Nr. <i>Part no.</i>	Rev.	Isolations- Ø <i>Insulation- Ø</i>	Farbe <i>Colour</i>	<i>Oil portion</i>
MVL		DELPHI		Kabel / Wire		

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
010C14		01				MIGRATED FROM MVL SYSTEM		J.COL	P.NUE	S.MUE
20JN16		02				MIGRATED FROM MVL SYSTEM		V.DUR	P.NUE	S.MUE
260C16	R	03				DRWING REWORKED		V.VEN	S.ANUF	M.SCH
13JA17	R	03	AA	-	BI	DATE AND NAME CHANGE		MSCH	HBR	RSCH

3D-VIEW M 1:1
3D-ANSICHT



DWG TYP CUSTOMER PART DRAWING	
WEIGHT (GR)	DISTR CODE
VOLUME (CM³)	
ROUTING	

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
DIN ISO 3302-1 M2

GD&T
ACCORDING TO:
DIN ISO 8015

REFERENCE
60993906

FIRST ANGLE PROJECTION

DO NOT
SCALE
USE MATH
DATA

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
Chennai, India

COPYRIGHT 2001 DELPHI CORPORATION AND/OR ITS AFFILIATES.
ALL RIGHTS RESERVED.
REVISED 2017

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION
AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION
OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA,
AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS,
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DIESE ZEICHNUNG IST EIGENTUM DER FIRMA DELPHI UND ENTHAELT DELPHI
VERTRAULICHE INFORMATIONEN. DIE REPRODUKTION, VERTEILUNG UND
NUTZUNG DIESES DOKUMENTES ODER DEREN ZUGEHÖRIGEN CAD DATEN, ODER
AUCH ALS KOMMUNIKATION VON BELIEBIGEN INHALT ZU ANDEREN, IST OHNE
BERECHTIGUNGSPRUEFUNG DURCH DIE DELPHI CORPORATION UNZULAESSIG.

DATE	
DR	St.Mueller
APVD1	Mueller
APVD2	G.May
APVD3	
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001
POTENTIELL GEFÄHRLICHE STOFFE UND REZYKLATANTEIL
GEMAESS DELPHI 10949001

MATERIAL

SIEHE BEMERKUNGEN / SEE NOTES

DRAWING NAME
EINZELDRAHTDICHT. GEHAUSE
1.5mm-KAMMER- Ø 3.6±0.1

SINGLE WIRE SEAL HOUSING
1.5mm-CAVITY- Ø 3.6±0.1

DRAWING NUMBER

15453990

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A2	10:1	1 OF 1	1 OF 1	R	03	AA