



SYMBOL DEFINITION		MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	15	
	LAST NO. USED	17	

CWS STATUS					REVISION HISTORY					AUTH	DR	APV/D	APV/D
DATE	STG	REV	N/P	CHG	ZONE								
14AP97	R	-	-	-	-	ALL PARTS - REDRAWN WITH NO PHYSICAL CHANGE - NO REV UPDATE REQ'D				970007	PHC	RRS	-
14AP97	R	-	-	-	-	15318038, 15318039 AND 15318040 - RELEASED TO REV "A"				970005	PHC	RRS	-
15N098	R	-	-	-	-	ALL PARTS - REDRAWN TO PD AND REVISED - REV LEVELS ADVANCED				190293	JTC	JHV	-
01DE03	R	01	-	-	-	ALL ACTIVE PARTS - ADDED VIEW TYPES SPECIFIC TO PART				249493	JS	JS	TM
02MR09	R	02	-	-	-	13753470 WAS PE180577, 13753471 WAS PE182115 AND RELEASED				407461	TAI	TAI	WTM
16OC09	R	03	-	-	-	13790534 - RELEASED AND ADDED TYPE 104 VIEW				409229	HCB	AUG	WTM
21DE09	R	04	-	-	-	13790534 - CABLE SIZE WAS 4 - 5 AND DIM E +/- 0.4 WAS 5.8				409673	JAR	JAR	WTM
11MY10	R	05	-	-	-	13753471 - CABLE DIA WAS 5.24-3.49; 13790534 - CABLE DIA WAS 4.3-3.4				410798	JTZ	JTZ	WTM
12JAI1	R	06	-	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES				412995	JEG	JAA	LHT
28JLI1	R	07	-	-	-	13753471 - ADDED CRIMPED ONTO 5 MM² NOTE				414952	JCF	JVM	WTM
08AU12	R	08	-	-	-	12020116, 12020782, 12034047, 12066271, 12084586, 12124085, 12129498, 15318038-40 AND 13753470-71, 13790534 - UPDATED MAT'L CALLOUT				419197	DCH	JVM	MAA
07AU14	R	09	-	-	-	33179130 - RELEASED				427214	JVR	JVM	JSM
19FE15	R	10	-	-	-	13753470-71 & 13790534 - ADDED TARNISH NOTE				428876	JVR	JVM	JSM
18JN15	R	11	-	-	-	12066270 MAKE OBSOLETE				429948	RCE	LES	VMR
19AU15	R	12	-	-	-	13753470, 13753471, 13790534, 33179130 - REVISED GEOMETRY				430422	AHG	AHG	TG




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN


TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN




CARRIER STRIP VIEW
SCALE 2:1




WING CONST I



WING CONST II



"PED" OPTIONAL FOR
EXISTING TOOLS



TYPE 101

PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SPEC	SIZE (MM²)	ID	DIA	TYPE	WING CONST	E
---	---	---	0.381X42.04	---	33179130	01	AA	AG PLATED COPPER ALLOY	3-2	13	3.8-2.45	103	11	4
---	---	---	0.381X42.04	---	13790534	02	AE	AG PLATED COPPER ALLOY	4-5	10	3.4-5.24	104	11	5.4
---	---	---	0.381X42.04	---	13753471	01	AF	AG PLATED COPPER ALLOY	5-3	11	3-4.09	103	1	4.6
---	---	---	0.381X42.04	---	13753470	01	AD	AG PLATED COPPER ALLOY	2-1	15	3.97-2.48	102	1	3.7
---	---	---	0.381X42.04	---	15318040	A4	-	TIN PLATED COPPER ALLOY	2-1	15N	3.97-2.48	102	1	3.7
---	---	---	0.381X42.04	---	15318039	A4	-	TIN PLATED COPPER ALLOY	0.5-0.35	21N	-	101	11	2.4±0.2
---	---	---	0.381X42.04	---	15318038	A4	-	TIN PLATED COPPER ALLOY	TWO 0.35	222N	2-1.35	101	11	3.6±0.2
---	---	---	0.381X42.04	---	12129498	B4	-	TIN PLATED COPPER ALLOY	3-2	13	3.8-2.45	103	11	4
---	---	---	0.381X42.04	---	12124085	A4	-	TIN PLATED COPPER ALLOY	0.8-0.5	19	3.12-2.03	101	1	3.2
---	---	---	0.381X42.04	---	12084586	B4	-	TIN PLATED COPPER ALLOY	5-3	11	5.24-3.49	103	1	4.6
---	---	---	0.381X42.04	---	12066271	B4	-	TIN PLATED COPPER ALLOY	0.5-0.35	21	3.2-2.03	101	11	2.4±0.2
12124085	A3	-	0.381X42.04	COPPER ALLOY	12056825	E1	-	TIN PLATED COPPER ALLOY	3	12	3.2-3.04	103	1	4.6
12066270	A4	-	0.381X42.04	COPPER ALLOY	12034047	D4	-	TIN PLATED COPPER ALLOY	0.8-0.5	19	3.12-2.03	101	1	3.2
12078175	B1	-	0.381X42.47	COPPER ALLOY	12020782	F4	-	TIN PLATED COPPER ALLOY	TWO 0.35	222	2-1.35	101	11	3.6±0.2
12020389	E3	-	0.381X42.04	COPPER ALLOY	12086281	E1	-	TIN PLATED COPPER ALLOY	0.35	22	2-1.35	101	11	2.2±0.2
---	---	---	0.381X42.47	---	12098117	C1	-	TIN PLATED COPPER ALLOY	5-3	11	5.24-3.49	102	1	4.6
12078174	A1	-	0.381X42.47	COPPER ALLOY	12020116	D4	-	TIN PLATED COPPER ALLOY	2-1	15	3.97-2.48	102	1	3.7
12020388	B3	-	0.381X42.04	COPPER ALLOY	12086115	C1	-	TIN PLATED COPPER ALLOY	0.8-0.5	19	3.12-2.03	101	1	3.2
UNPLATED														
PLATED														

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- MATING COMPONENTS OR EQUIVALENT: TERMINAL 12015823

- TERMINAL 13753471 WHEN CRIMPED ONTO 5MM² 105 STRAND CONDUCTOR, CONDUCTOR WINGS MUST BE SOLDERED.

- 0.4 R PERMISSIBLE ON ALL "SHARP" CORNERS.

- "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIES NUMBERS (P01,P02,P03,ETC.)

- FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER, TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE PERFORMANCE OF THE PART.

LINE DRAWN THROUGH A PART NUMBER	
INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (OMP)	
DISTR CODE	
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE 2003 SUPPLEMENT AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNING OF FEATURES MAY BE OBTAINED SEPARATELY. REVIEWS OF DATA REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	
ANGULAR TOLERANCE 12°	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WARREN, OH	
COPYRIGHT 1997 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS CONTENTS OR DATA, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	
DR	
APV01 H. CASTRILLON	
APV02 R. RAMOS S.	
APV03 DOUG CUMMINGS	
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT, PER DELPHI 10449901	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI TERM M W/P 280	
DRAWING NUMBER	
12020114	
SIZE A0	
SCALE 10:1	
FRAME NO 1 OF 1	
SHEET NO 1 OF 1	
STG REV N/P	
R 12	