


PART NO.	MAX BUNDLE DIA.	"L" LENGTH APPROX.	"W" WIDTH REF	"T" THICKNESS REF	"A"	"B"	MIN LOOP TENSILE
WIT-50SR	1-1/2 [38.1]	6 [152.4]	.19 [4.8]	.05 [1.3]	.21 [5.3]	.31 [7.9]	50 lbf [22.7kgf]
WIT-50RR	2 [50.8]	8 [203.2]			.22 [5.6]	.34 [8.6]	
WIT-50LR	3 [76.2]	11-21/32 [295.9]					
WIT-120SR	2 [50.8]	8-1/2 [215.9]	.30 [7.6]	.07 [1.8]	.29 [7.4]	.51 [13]	120 lbf [54.4 kgf]
WIT-120RR	4-1/4 [108]	15 [381]					
WIT-120LR	5-7/8 [149.2]	21-1/4 [539.8]					



- NOTES:
- 1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
COLOR: NATURAL.
 - 2. MATERIAL: UV STABILIZED NYLON 6/6 UL 94 V-2 (RMS-46).
COLOR BLACK.
TO ORDER USE P/N: WIT-XXX-UVB.
 - 3. MATERIAL: NYLON 6/6 UL 94 V-0 (RMS-75), COLOR NATURAL.
AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER USE PART P/N: WIT-XXX-V0
 - 3. COLORS: GREEN (-GN), BLUE (-BL), YELLOW (-YL)
AND RED (-RD) AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER ADD COLOR SUFFIX TO PART NO.

E	SEE CO 200161 FOR CHANGES	SK	04/15/08
D	REDRAWN, SEE CO 200085 FOR CHANGES	SK	12/07/07
-	SEE ENGINEERING FOR REV A-C	---	-----
REV.	DESCRIPTION	ENGR.	DATE

TITLE: RELEASABLE WIRE TIES					DWG IN IN [MM]	
CREATED USING SOLIDWORKS	FILE #: WIT-XXXXR		DWN: S.K.	APP: D.Z.	FINAL	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: B	DT: 12/07/07	CHKD: R.T.	PART #	PRINT TYPE
RE: RICHCO INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		SEE TABLE		CA