

CUSTOMER DRAWING


P/N: 3800S 175/-6


REV
N

PART NUMBER	MATERIAL	FINISH
3800S 175A-6	.025 THICK BRASS	PRETINNED
3800S 175AB-6	.025 THICK BRASS	NONE
3800S 175AD-6	.025 THICK BRASS	POST-TIN

- NOTES:
1. CMA RANGE: 12000 TO 29000.
 2. FOR PIGTAIL SPLICES USED IN A BENCH APPLICATOR, ADD SUFFIX "PP" TO PART NUMBER (i.e. 3800S 175A-6PP), SEE FIGURE 1 FOR REELING.
 3. FOR THROUGH SPLICES USED IN A BENCH APPLICATOR, THE PART NUMBER REMAINS THE SAME AS IN THE TABLE (i.e. 3800S 175A-6). SEE FIGURE 2 FOR REELING.
 4. FOR PIGTAIL AND THROUGH SPLICES USED IN A SLIM-LINE AIR PRESS, THE PART NUMBER REMAINS THE SAME AS IN THE TABLE (i.e. 3800S 175A-6). SEE FIGURE 2 FOR REELING.
 5. PAPER INTERLEAVING ADDED TO REDUCE TANGLING IN REELS.

ARK-LES
UNCONTROLLED



				PRINT DIST.	PROD. REL. ECR 9458 11/10/1980		CHK'D DD 11/17/06	TOLERANCES UNLESS OTHERWISE SPECIFIED	<div>Ark-Les CORPORATION</div> <div>STOUGHTON, MA</div>
					QUOTE REL.				
				DEPT	#	DRAWN BY D.O'NEILL 11/03/06		APP.	ORIGINAL IF RED
				ENG	X	SUPERSEDES DWG. DATED: 5/22/01		ES 11-17-06	
				SALES		SCALE 3:1		DO NOT SCALE PRINT	METRIC ±0.25mm
				STO	X	MATERIAL: SEE TABLE			ANGLES ±1°
N	REV/REDRWN ECR# S000127	11/03/06	DON	RAL					
				JZ		FINISH: SEE TABLE			<div> 3RD ANGLE PROJECTION DWG SIZE B</div>
				CHINA					
REV.	DESCRIPTION	DATE	DR.						PART NAME CUSTOMER DRAWING SPLICE TERMINAL
									CAD#: 3800S_175-6-REVN_CUST
									P/N: 3800S 175/-6
									REV N