

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - 03JUL2019



ALL RIGHTS RESERVED.

PROJECT	PRJ-17-000905364
PART NO.	2352906-X
DESCRIPTION	12 PORT MANAGED POE SWITCH RACK MOUNTED WITH 10GB/S OPTION
CUSTOMER	GENERAL MARKET

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	24JUL2019	GK	SE

NOTES:



1. LEADING EN50155-COMPLIANT ETHERNET SWITCH FOR INDUSTRIAL APPLICATIONS, SUCH AS ROLLING STOCK, VEHICLE, AND RAILWAY APPLICATIONS.
2. M12 CONNECTORS TO GUARANTEE RELIABLE OPERATION AGAINST ENVIRONMENTAL DISTURBANCES.
3. RIGID IP-30 HOUSING DESIGN



PICTORIAL VIEW

FUNCTION	CONNECTOR ON SWITCH	REMARKS
RELAY	M12 FEMALE A5 CODED	3A AT 24VDC
CONSOLE	M12 FEMALE A5 CODED	115200bps, 8, N, 1
POWER	M12 FEMALE 4P S-CODED	72–110VDC
PORTS G1 TO G12	M12 FEMALE 8P X-CODED	—

2	2352906-2	12-PORT RACK MOUNTED MANAGED 10 GIGABIT POE ETHERNET SWITCH WITH 2XBYPASS, M12 X CONNECTOR AND 72-110VDC INPUT	12	8	10/100/1000 10 Gb Base-T(X)	2X	72-110VDC
1	2352906-1	12-PORT RACK MOUNTED MANAGED GIGABIT POE ETHERNET SWITCH WITH 2XBYPASS, M12 X CONNECTOR AND 72-110VDC INPUT			10/100/1000 Base-T(X)		
SL. NO.	PART NO.	DESCRIPTION	NO. OF PORTS	POE PORTS	SPEED	BY PASS	INPUT POWER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA HV 24JUL2019 CHK S. EGBERT 24JUL2019 APVD S. EGBERT 24JUL2019 PRODUCT SPEC — APPLICATION SPEC — WEIGHT 0		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± ± — FINISH —		NAME 12 PORT MANAGED POE SWITCH RACK MOUNTED WITH 10GB/S OPTION — SIZE A2	
MATERIAL —		CAGE CODE 00779		DRAWING NO G=2352906	
		RESTRICTED TO —		SCALE NTS	
		SHEET 1 OF 1		REV A	