


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TOOL	ANVIL SLOT WIDTH (STRAP SIZE)	ANVIL MARKS	SETSHEAR FINGER MARKS	TOOL TENSION SETTING
MTRTLS	3/16" (4.6mm) – S	1 MARK	2 MARKS	S
	1/4" (6.4mm) – LH	2 MARKS	2 MARKS	LH
MTRTH	5/16" (7.9mm) – H	NO MARK	1 MARK	H



NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT MTRTH tool installs MRT and MRS Ball Lock ties in widths of 5/16" (7.9mm) Heavy (H) cross sections.

PANDUIT MTRTLS tool installs MRT and MRS Ball Lock ties in widths of 3/16" (4.6mm) Standard (S) cross sections. An Anvil is included, which can be changed for installing MRT and MRS ties in widths of 1/4" (6.4mm) Light-Heavy (LH) cross-sections.

TOOL FEATURES INCLUDE:

- Adjustable detent mechanism
- Smooth cable tie cut-off
- Tie tensioning mechanism


CABLE TIE CODE:

MRT = Metal Retained Tension Tie

MRS = Metal Radial Seal Retained Tension Tie

TOOL WEIGHT = 47 OZ. (1329 GRAMS)

DIMENSIONS IN PARENTHESES ARE METRIC.



REV	DATE	BY	CHK'D	DESCRIPTION	ECN	- R	CUST	SUP
01	12-3-18	TCAV	JADE	REMOVED CHANGEOVER KIT CALLOUTS	42834	--	JADE	
00	6-13-07	BLR	BJPU	RELEASED	4232	--	JRWA	

PANDUIT CORP. TINLEY PARK, ILLINOIS

**MTRTH and MTRTLS
CUSTOMER DRAWING**

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.x) ± --- (.xxx) ± ---
(.xx) ± --- ANGLES ± ---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE
PROJECTION.

DRAWN BY:
BLR

DATE:
6-13-07

CHK'D:
BJPU

MATL:

SCALE

NONE

DRAWING NO.

TM25278B01

DWG
B
SIZE