


Customer drawing

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	07/24/09	IP
2	HK--	Update spec.	05/26/14	IP
3	HK--	Update Dimension.	11/03/17	IP
4	HK--	Adding Dimension.	04/09/19	IP

D-SUB TECHNICAL DATA

SPECIFICATIONS

1. Current Rating: 3 Ampere per Contact
2. Contact Resistance: 25 Milliohms Max.
3. Operating Voltage: 250 VAC Max.
4. Recommended Wire Range: 24~28 AWG.
5. Contact: Copper Alloy.
6. Plating: Refer to part numbers

PRODUCT CODE

L 17 HR D2 M XX XXX

L: RoHS Compliance

Wire Size:
24 to 28AWG

Contact Type:
M: Male

Packaging:
5K=Reel of 5000 cts
(right feed reel)
5G=Reel of 5000 cts
(left feed reel)
10K=Reel of 10000 cts
(right feed reel)
10G=Reel of 10000 cts
(left feed reel)

Full Gold Plating:
01=Flash gold
02=0.375um(15u")
04=0.76um(30u")
Selective gold Plating:
11=Flash gold+2um(78u")Sn
12=0.375um(15u") Au+2um(78u")Sn
14=0.76u(30u") Au+2um(78u")Sn

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE
U.S.	METRIC	DRAWN	DATE	
.X +/-	0.50	Pat. Liu	04/09/19	
.XX +/-	0.30	CHECKED Tony Tang	04/09/19	
.XXX +/-	0.20	CHECKED		
FRACTIONS +/-	5'			
ANGLES +/-				
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :		
REMOVE SHARP EDGES		ANGLE OF PROJECTION		
DIMENSIONS				
U.S.	INCHES			
METRIC	MM			

Amphenol

TITLE

CONTACT, HR Series

SIZE	DRAWING NO.	REV.
A4	L17HRD2MXXXXX	4
SCALE	NONE	SHEET 1 OF 1