




Customer drawing



RECOMMENDED P.C.B. LAYOUT
TOLERANCE:±0.05MM

NO.	A ± 0.38	B ± 0.25	C ± 0.13	D ± 0.13	E ± 0.25
15S	30.81	24.99	16.33	2.29	0.25
26S	39.19	33.32	24.66	2.29	0.51
44S	53.04	47.04	38.38	2.29	0.51
62S	69.32	63.50	54.84	2.41	0.58



D-SUB TECHNICAL DATA

SHELL : SPCC, 80u" min nickel over 50u" min Copper
BODY : PA9T UL 94V-0 Color: Black
CONTACTS : Copper Alloy
Gold over 50u" min nickel on mating area.
100u" min tin over 50u" min nickel on solder area.
BOARDLOCK: Copper alloy, Tin plated.
REAR NUT: Copper alloy, Nickel plated.
ELECTRICAL : Voltage rating 250 V Rms Max.
Current rating 3A.
Withstanding Voltage >1000 V Rms
Insulation resistance >1000 M Ohms
Contact resistance 25 mOhms max.
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 17HT H X S 4R X C

L: RoHS Compliant

High density	
--------------	--


Shell size:
E (15 ways)
A (26 ways)
B (44 ways)
C (62 ways)

Contact type:
S = Socket

Packaging	C = Plastic Tray
-----------	------------------

Contact plating: 1 = gold flash 2 = 15 μ" 4 = 30 μ"

Mounting options:
4R = rear insert 4-40

UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	
TOLERANCES					
U.S.		METRIC			
.X +/-		0.50		DRAWN <i>Pekka Lau</i> 10/06/01	
.XX +/-		0.30		CHECKED <i>Tony Tang</i> 10/06/01	
.XXX +/-		0.20		CHECKED	
FRACTIONS +/-					
ANGLES +/-		5°			
FOR MATERIALS AND FINISHES SEE NOTES					
DRAWING FILE :					
REMOVE SHARP EDGES			ANGLE OF PROJECTION		
DIMENSIONS					
U.S.		INCHES			
METRIC		MM			

Amphenol

TITLE

D-SUB R/A Female connector

SIZE	DRAWING NO.	REV.
A4	L17HTHXS4RXC	2
SCALE	NONE	SHEET 1 OF 1